

MC 1000E-MM WDM A - FO converters



1330588

<https://www.phoenixcontact.com/us/products/1330588>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic converter with SC simplex connection (1310 nm) for 100Base-TX to multimode fiber optics, DIN rail mountable, extended temperature range, redundant power supply, IECEx, ATEX, UL HazLoc, IEC 61850, IEEE 1613, DNV.

Product description

The MC 1000E-MM WDM A media converter comes with one 10/100 Mbps twisted-pair RJ45 port and one 100 Mbps WDM multi-mode fiber port with an SC-simplex connector, ruggedized EMI protection, and wide temperature range.

Your advantages

- Auto MDI/MDI-X switch-over
- Data transfer rates of 100 Mbps
- Link fault pass through (LFPT) function for easy connection monitoring
- Network structure according to IEC 61850-3
- IEEE 1613
- Class 1 laser product complies with EN 60825-1

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1330588 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN06 |
| Product key | DNC314 |
| GTIN | 4063151627058 |
| Weight per piece (including packing) | 283.2 g |
| Weight per piece (excluding packing) | 180 g |
| Customs tariff number | 85176200 |
| Country of origin | CA |

MC 1000E-MM WDM A - FO converters



1330588

<https://www.phoenixcontact.com/us/products/1330588>

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Product properties

| | |
|----------------|--|
| Product type | Media converter |
| Product family | MC 1000E |
| MTTF | 69.1 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) |
| | 508.3 Years (SN 29500 standard, temperature 25°C, operating cycle 21%) |
| | 702.5 Years (Telcordia standard, temperature 25 °C, operating cycle 100 % (7 days a week, 24 hours a day)) |

Electrical properties

Supply

| | |
|-----------------------------|-------------------------|
| Supply voltage range | 12 V DC ... 57 V DC |
| Nominal supply voltage | 24 V DC |
| | 48 V DC |
| Typical current consumption | 20 mA (24 V DC) |
| Max. current consumption | 170 mA (12 V DC, 75 °C) |

Output data

Signal

| | |
|-----------------------|--|
| Voltage output signal | 12 V DC ... 48 V DC (depending on the input voltage) |
| Current output signal | 100 mA |

Connection data

Supply

| | |
|---|---|
| Connection method | Push-in spring connection |
| Single conductor/terminal point, rigid | 0.2 mm ² ... 2.5 mm ² |
| Single-wire/terminal point, flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible [AWG] | 24 ... 12 |
| Stripping length | 10.00 mm |

Interfaces

| | |
|--------|----------|
| Signal | Ethernet |
|--------|----------|

Data: optical FO

| | |
|----------------------------|---------|
| Transmit capacity, minimum | -10 dBm |
| Transmit capacity, maximum | 0 dBm |

MC 1000E-MM WDM A - FO converters



1330588

<https://www.phoenixcontact.com/us/products/1330588>

| | |
|---|---|
| Transmission length incl. 3 dB system reserve | 2 km |
| Connection method | SC simplex |
| Wavelength | 1310 nm (transmit) 1550 nm (receive) |
| Minimum receiver sensitivity | -28 dBm |
| Maximum receiver sensitivity | 0 dBm |
| Transmission medium | Multi-mode fiberglass |

Data: Ethernet interface, 10/100Base-T(X) in accordance with IEEE 802.3

| | |
|------------------------|-------------------------------|
| Transmission speed | 10/100 Mbps |
| Connection method | RJ45 jack, shielded |
| No. of channels | 1 |
| Transmission length | 100 m (shielded twisted pair) |
| Transmission medium | Copper |
| Signal LEDs | LNK/ACT, SPD, Err, US, US2 |
| Auto-negotiation modes | Auto |
| Link through | Link fault pass through |
| MDI-/MDI-X switchover | Auto-MDI(X) |

Dimensions

| | |
|--------|---------|
| Width | 22.5 mm |
| Height | 125 mm |
| Depth | 90 mm |

Material specifications

| | |
|------------------|---|
| Housing material | Polyamide fiber reinforced Aluminum / steel sheet DC01 |
|------------------|---|

Cable/line

FO cable

| | |
|-------------|--|
| Fiber types | 50/125 µm 62.5/125 µm Fiberglass |
|-------------|--|

Mechanical tests

| | |
|--|------------------------------------|
| Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6 | : 5g, 150 Hz, Criterion 3 |
| Shock in accordance with EN 60068-2-27/IEC 60068-2-27 | : 30g, 11 ms half-sine shock pulse |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP30 |
| Ambient temperature (operation) | -40 °C ... 75 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

MC 1000E-MM WDM A - FO converters



1330588

<https://www.phoenixcontact.com/us/products/1330588>

| | |
|----------------------------------|--|
| Altitude | ≤ 2000 m (in acc. with UL) |
| Permissible humidity (operation) | 10 % ... 95 % (non-condensing) |
| Shock | 300 m/s ² , 11 ms (IEC 60068-2) |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

UL, USA/Canada

| | |
|----------------|--|
| Identification | Class I, Division 2, Groups A, B, C, and D, T4 |
| | Class I, Zone 2, IIC T4 |

IECEX

| | |
|----------------|-------------------|
| Identification | Ex ec IIC T4 Gc |
| Certificate | IECEX UL 25.0019X |

ATEX

| | |
|----------------|--------------------------|
| Identification | Ⓜ II 3 G Ex ec IIC T4 Gc |
| Certificate | UL 25 ATEX 3348X |

EMC data

| | |
|-------------------------------|---|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| Noise immunity | IEC 61850-3, IEEE 1613 |

Electrostatic discharge

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-2 |
|-----------------------|--------------|

Electrostatic discharge

| | |
|----------|-------------|
| Comments | Criterion B |
|----------|-------------|

Electromagnetic HF field

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-3 |
|-----------------------|--------------|

Electromagnetic HF field

| | |
|----------|-------------|
| Comments | Criterion A |
|----------|-------------|

Fast transients (burst)

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-4 |
|-----------------------|--------------|

Fast transients (burst)

| | |
|----------|-------------|
| Comments | Criterion A |
|----------|-------------|

Surge current load (surge)

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-5 |
|-----------------------|--------------|

Surge current load (surge)

| | |
|----------|-------------|
| Comments | Criterion B |
|----------|-------------|

Conducted interference

MC 1000E-MM WDM A - FO converters



1330588

<https://www.phoenixcontact.com/us/products/1330588>

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-6 |
|-----------------------|--------------|

Conducted interference

| | |
|----------|-------------|
| Comments | Criterion A |
|----------|-------------|

Emitted interference

| | |
|-----------------------|----------|
| Standards/regulations | EN 55032 |
|-----------------------|----------|

Mounting

| | |
|-----------------------|--|
| Mounting type | DIN rail mounting |
| Mounting position | on horizontal DIN rail NS 35 in acc. with EN 60715 |
| Useable DIN rail type | DIN rail: 35 mm |

MC 1000E-MM WDM A - FO converters



1330588

<https://www.phoenixcontact.com/us/products/1330588>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1330588>



cULus Listed

Approval ID: E238705

BSH

Approval ID: BSH Nr. 1176



IECEE CB Scheme

Approval ID: CA-11671-M1-UL

BSH

Approval ID: BSH Nr. 1176



cULus Listed

Approval ID: E238705

DNV

Approval ID: TAA00003RU

DNV

Approval ID: TAA00003RU



IECEx

Approval ID: IECEx UL 25.0019X



ATEX

Approval ID: UL 25 ATEX 3348X



cULus Listed

Approval ID: E196811



cULus Listed

Approval ID: E196811

MC 1000E-MM WDM A - FO converters



1330588

<https://www.phoenixcontact.com/us/products/1330588>



IECEx

Approval ID: IECEx UL 25.0019X



ATEX

Approval ID: UL 25 ATEX 3348X

MC 1000E-MM WDM A - FO converters



1330588

<https://www.phoenixcontact.com/us/products/1330588>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170411 |
| ECLASS-15.0 | 19170411 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001467 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43223323 |
|-------------|----------|

MC 1000E-MM WDM A - FO converters



1330588

<https://www.phoenixcontact.com/us/products/1330588>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com