

ANT-OMNI-2459-04 - Antenna

1284780

<https://www.phoenixcontact.com/us/products/1284780>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multiband omnidirectional antenna for freely mobile applications, compact design, frequency band: 2.4 GHz / 5 GHz / 6 GHz, gain: 2.0 dBi / 2.5 dBi / 3.0 dBi, degree of protection: IP68/IP69K, shock- and vibration-resistant, connection: N (male)

Your advantages

- Compact design
- Ideally suited for freely mobile applications with 2.4 GHz, 5 GHz, or 6 GHz
- Universal use with the wide frequency range
- Shock- and vibration-resistant

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1284780 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN23 |
| Product key | DNN2Z1 |
| GTIN | 4063151490621 |
| Weight per piece (including packing) | 49.6 g |
| Weight per piece (excluding packing) | 49.5 g |
| Customs tariff number | 85177100 |
| Country of origin | CN |

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Product properties

| | |
|---------------------------|-------------------------------|
| Product type | Antenna |
| Radiation characteristics | Omnidirectional |
| Gain | 1.5 dBi (1.7 GHz ... 2.0 GHz) |
| | 2 dBi (2.0 GHz ... 2.7 GHz) |
| | 1.5 dBi (2.7 GHz ... 4.2 GHz) |
| | 2.5 dBi (4.9 GHz ... 5.9 GHz) |
| | 3 dBi (5.9 GHz ... 7.1 GHz) |
| Polarization | Linear vertical |

Electrical properties

| | |
|--|---------------------|
| Frequency band | 2.4 GHz |
| | 5 GHz |
| | 6 GHz |
| Frequency range | 1.7 GHz ... 7.1 GHz |
| Impedance | 50 Ω |
| Maximum capacity | 120.00 W |
| Voltage standing wave ratio VSWR in a 50 Ω system | ≤ 2.00 |

Connection data

Connection technology

| | |
|-------------------|----------|
| Connection method | N (male) |
|-------------------|----------|

Dimensions

| | |
|----------|-------|
| Length | 55 mm |
| Diameter | 22 mm |

Material specifications

| | |
|--|--|
| Material | ASA, Acrylic ester styrene-acrylonitrile |
| Flammability rating according to UL 94 | HB |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP68/IP69K |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

ANT-OMNI-2459-04 - Antenna



1284780

<https://www.phoenixcontact.com/us/products/1284780>

Approvals

Electronic devices in rail vehicles

| | |
|-----------------------|---|
| Shock (operation) | In accordance with EN 61373 (category 1, class B) |
| Vibration (operation) | In accordance with EN 61373 (category 1, class B) |

Standards and regulations

| | |
|--------------------------|-------------------------------------|
| Standards/specifications | EN 45545-2 |
| Note | Fire protection on railway vehicles |
| Standards/specifications | EN 50155 |
| Note | Railway application |

Mounting

| | |
|---------------|--------------------------|
| Mounting type | Control cabinet mounting |
| Assembly note | Accessories required |
| | Outdoors and indoors |

ANT-OMNI-2459-04 - Antenna


1284780

<https://www.phoenixcontact.com/us/products/1284780>



Drawings

Schematic diagram



Installation example

ANT-OMNI-2459-04 - Antenna



1284780

<https://www.phoenixcontact.com/us/products/1284780>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19070105 |
| ECLASS-15.0 | 19070105 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001698 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43223100 |
|-------------|----------|

1284780

<https://www.phoenixcontact.com/us/products/1284780>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-25 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 2.891 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com