

MC 1100T-SFP - FO converters

1330902

<https://www.phoenixcontact.com/us/products/1330902>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Gigabit fiber optic converter with SFP port for 1000Base-T, DIN rail mountable, extended temperature range, redundant power supply.

Product description

The MC 1100T- SFP gigabit media converter comes with one 10/100/1000 Mbps twisted-pair RJ45 port and one 100/1000 Mbps SFP port and wide temperature range.

Your advantages

- Auto MDI/MDI-X switch-over
- Data transfer rates of 1000 Mbps
- Link fault pass through (LFPT) function for easy connection monitoring

Commercial data

Item number	1330902
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN06
Product key	DNC315
GTIN	4063151626792
Weight per piece (including packing)	265.3 g
Weight per piece (excluding packing)	180 g
Customs tariff number	85176200
Country of origin	MY

MC 1100T-SFP - FO converters



1330902

<https://www.phoenixcontact.com/us/products/1330902>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Media converter
Product family	MC 1000T
MTTF	63.9 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
	481.2 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	333.7 Years (Telcordia standard, temperature 25 °C, operating cycle 100 % (7 days a week, 24 hours a day))

Electrical properties

Maximum power dissipation for nominal condition	1.5 W
---	-------

Supply

Supply voltage range	12 V DC ... 57 V DC
Nominal supply voltage	24 V DC
	48 V DC
Typical current consumption	62 mA (24 V DC)
Max. current consumption	170 mA (12 V DC, 75 °C)

Output data

Signal

Voltage output signal	12 V DC ... 48 V DC (depending on the input voltage)
Current output signal	100 mA

Connection data

Supply

Connection method	Push-in spring connection
Single conductor/terminal point, rigid	0.2 mm ² ... 2.5 mm ²
Single-wire/terminal point, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	24 ... 12
Stripping length	10.00 mm

Interfaces

MC 1100T-SFP - FO converters



1330902

<https://www.phoenixcontact.com/us/products/1330902>

Signal	Ethernet
--------	----------

Data: optical FO

Connection method	SFP
Transmission medium	depending on the SFP module used

Data: Ethernet interface, 10/100/1000Base-T(X) in accordance with IEEE 802.3

Transmission speed	10/100/1000 Mbps
Connection method	RJ45 jack, shielded
No. of channels	1
Transmission length	100 m (twisted pair, shielded)
Transmission medium	Copper
Signal LEDs	LNK/ACT, SPD, Err, US, US2
Auto-negotiation modes	Auto
Link through	Link fault pass through
MDI-/MDI-X switchover	Auto-MDI(X)

Dimensions

Width	22.5 mm
Height	125 mm
Depth	90 mm

Material specifications

Color (Housing)	gray (RAL 7042)
Color (Cover)	light gray (RAL 7035)
Housing material	Polyamide fiber reinforced Aluminum / steel sheet DC01

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Operation: 5g, 150 Hz, Criterion 3
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Operation: 30g, 11 ms half-sine shock pulse

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m (in acc. with UL)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Shock	300 m/s ² , 11 ms (IEC 60068-2)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

MC 1100T-SFP - FO converters



1330902

<https://www.phoenixcontact.com/us/products/1330902>

UL, USA/Canada

Identification	Class I, Division 2, Groups A, B, C, and D, T4
----------------	--

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Comments	Criterion B
----------	-------------

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Electromagnetic HF field

Comments	Criterion A
----------	-------------

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Fast transients (burst)

Comments	Criterion A
----------	-------------

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Surge current load (surge)

Comments	Criterion B
----------	-------------

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

Comments	Criterion A
----------	-------------

Emitted interference

Standards/regulations	EN 55032
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715
Useable DIN rail type	DIN rail: 35 mm

MC 1100T-SFP - FO converters



1330902

<https://www.phoenixcontact.com/us/products/1330902>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1330902>



cULus Listed

Approval ID: E238705

BSH

Approval ID: BSH Nr. 1176



IECEE CB Scheme

Approval ID: CA-11671-M1-UL

DNV

Approval ID: TAA00003RU



cULus Listed

Approval ID: E196811

MC 1100T-SFP - FO converters



1330902

<https://www.phoenixcontact.com/us/products/1330902>

Classifications

ECLASS

ECLASS-13.0	19170411
ECLASS-15.0	19170411

ETIM

ETIM 10.0	EC001467
-----------	----------

UNSPSC

UNSPSC 21.0	43223323
-------------	----------

MC 1100T-SFP - FO converters



1330902

<https://www.phoenixcontact.com/us/products/1330902>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com