

# ANT-OMNI-2459-04 - Antenna

1284780

<https://www.phoenixcontact.com/us/products/1284780>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multiband omnidirectional antenna for freely mobile applications, compact design, frequency band: 2.4 GHz / 5 GHz / 6 GHz, gain: 2.0 dBi / 2.5 dBi / 3.0 dBi, degree of protection: IP68/IP69K, shock- and vibration-resistant, connection: N (male)

## Your advantages

- Compact design
- Ideally suited for freely mobile applications with 2.4 GHz, 5 GHz, or 6 GHz
- Universal use with the wide frequency range
- Shock- and vibration-resistant

## Commercial data

Item number	1284780
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNN2Z1
GTIN	4063151490621
Weight per piece (including packing)	49.6 g
Weight per piece (excluding packing)	49.5 g
Customs tariff number	85177100
Country of origin	CN

1284780

<https://www.phoenixcontact.com/us/products/1284780>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Antenna
Radiation characteristics	Omnidirectional
Gain	1.5 dBi (1.7 GHz ... 2.0 GHz)
	2 dBi (2.0 GHz ... 2.7 GHz)
	1.5 dBi (2.7 GHz ... 4.2 GHz)
	2.5 dBi (4.9 GHz ... 5.9 GHz)
	3 dBi (5.9 GHz ... 7.1 GHz)
Polarization	Linear vertical

### Electrical properties

Frequency band	2.4 GHz
	5 GHz
	6 GHz
Frequency range	1.7 GHz ... 7.1 GHz
Impedance	50 $\Omega$
Maximum capacity	120.00 W
Voltage standing wave ratio VSWR in a 50 $\Omega$ system	$\leq 2.00$

### Connection data

#### Connection technology

Connection method	N (male)
-------------------	----------

### Dimensions

Length	55 mm
Diameter	22 mm

### Material specifications

Material	ASA, Acrylic ester styrene-acrylonitrile
Flammability rating according to UL 94	HB

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP68/IP69K
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

# ANT-OMNI-2459-04 - Antenna



1284780

<https://www.phoenixcontact.com/us/products/1284780>

## Approvals

### Electronic devices in rail vehicles

Shock (operation)	In accordance with EN 61373 (category 1, class B)
Vibration (operation)	In accordance with EN 61373 (category 1, class B)

## Standards and regulations

Standards/specifications	EN 45545-2
Note	Fire protection on railway vehicles
Standards/specifications	EN 50155
Note	Railway application

## Mounting

Mounting type	Control cabinet mounting
Assembly note	Accessories required
	Outdoors and indoors

# ANT-OMNI-2459-04 - Antenna


1284780

<https://www.phoenixcontact.com/us/products/1284780>



## Drawings

Schematic diagram



Installation example

# ANT-OMNI-2459-04 - Antenna



1284780

<https://www.phoenixcontact.com/us/products/1284780>

## Classifications

### ECLASS

ECLASS-13.0	19070105
ECLASS-15.0	19070105

### ETIM

ETIM 10.0	EC001698
-----------	----------

### UNSPSC

UNSPSC 21.0	43223100
-------------	----------

1284780

<https://www.phoenixcontact.com/us/products/1284780>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	2.891 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)