

WP 6070-WVPS - Web panel



1290800

<https://www.phoenixcontact.com/us/products/1290800>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP66 Touch panel with 7.0-inch widescreen (16:9) VGA, PCAP display, Software: Qt Browser



Your advantages

- Easy startup – just enter the IP and URL
- Flexible, thanks to open web standard and free choice of web server and visualization software
- No security updates are required for JAVA or Flash plug-ins thanks to HTML5
- Ideal for use with PLCnext Engineer or CODESYS
- Embedded Linux operating system
- Visualization of self-programmed JavaScript applications possible

Commercial data

Item number	1290800
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR17
Product key	DRCADF
GTIN	4063151522568
Weight per piece (including packing)	2,500 g
Weight per piece (excluding packing)	1,400 g
Customs tariff number	84714100
Country of origin	TW

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm® Cortex®-A53, 1.6 GHz
Operating system	Yocto/Linux®
Data storage system	Flash eMMC, 8 GB
Slots	1x microSD

Display

Display type	17.8 cm / 7"-TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	500 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	89.00 °
Reading angle right	89.00 °
Reading angle top	89.00 °
Reading angle bottom	89.00 °

Interfaces

Interfaces	2x USB 2.0
	1x USB 3.0, Typ C
	1x COM (RS-232/422/485)
Optional interfaces	Without optional interface
Network	1 x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without bus system

System properties

User software	QT browser
---------------	------------

System requirements

Runtime system	Qt Browser
----------------	------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Supply voltage (DC)	24 V DC \pm 20%
Supply voltage range	18 V DC ... 32 V DC
Power supply unit	24 V DC \pm 20 %
Max. current consumption	1.81 A (24 V DC)
Typical current consumption	0.61 A (24 V DC)

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Color (Housing)	white aluminium (RAL 9006)
Material front plate	Aluminum (natural anodized)
Housing material	Aluminum cast alloy, powder-coated

Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 85 % (non-condensing)
Shock	15g with 11 ms impulse
Vibration (operation)	1g

Dimensions

External dimensions

Width / Height / Depth	202 mm / 146 mm / 51 mm (Dimensions of the front plate)
------------------------	---

Installation dimensions

Width / Height / Installation depth	195 mm / 139 mm / (Installation cutout)
-------------------------------------	---

1290800

<https://www.phoenixcontact.com/us/products/1290800>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1290800>



IECEE CB Scheme
Approval ID: US-39088-UL



UL Listed
Approval ID: E238705



cUL Listed
Approval ID: E238705



IECEE CB Scheme
Approval ID: US-39088-UL



cUL Listed
Approval ID: E238705



UL Listed
Approval ID: E238705

1290800

<https://www.phoenixcontact.com/us/products/1290800>

Classifications

ECLASS

ECLASS-13.0	27330201
ECLASS-15.0	27330201

ETIM

ETIM 10.0	EC001412
-----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

1290800

<https://www.phoenixcontact.com/us/products/1290800>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

EF3.1 Climate Change

CO2e kg	167.775 kg CO2e
---------	-----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com