

WP 6101-WXPS - Web panel



1290801

<https://www.phoenixcontact.com/us/products/1290801>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP66 Touch panel with 10.1-inch widescreen (16:9) XGA, PCAP display, Software: Qt Browser



Your advantages

- Easy startup – just enter the IP and URL
- Flexible, thanks to open web standard and free choice of web server and visualization software
- No security updates are required for JAVA or Flash plug-ins thanks to HTML5
- Ideal for use with PLCnext Engineer or CODESYS
- Embedded Linux operating system
- Visualization of self-programmed JavaScript applications possible

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1290801 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DR17 |
| Product key | DRCADF |
| GTIN | 4063151523039 |
| Weight per piece (including packing) | 3,400 g |
| Weight per piece (excluding packing) | 1,900 g |
| Customs tariff number | 84714100 |
| Country of origin | TW |

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Product properties

| | |
|--------------|----------------|
| Product type | Operator panel |
|--------------|----------------|

Computer data

| | |
|---------------------|---------------------------|
| Processor | Arm® Cortex®-A53, 1.6 GHz |
| Operating system | Yocto/Linux® |
| Data storage system | Flash eMMC, 8 GB |
| Slots | 1x microSD |

Display

| | |
|-----------------------|--|
| Display type | 25.7 cm / 10.1"-TFT |
| Screen resolution | 1280 x 800 Pixel(s) (WXGA) |
| Touch technology | projective-capacitive (PCAP) |
| Display lighting type | LED |
| Brightness | 500 cd/m ² typical (adjustable) |
| MTBF | 50000 h |
| Color spectrum | 16.7 million colors |
| Reading angle left | 85.00 ° |
| Reading angle right | 85.00 ° |
| Reading angle top | 85.00 ° |
| Reading angle bottom | 85.00 ° |

Interfaces

| | |
|---------------------|---------------------------------------|
| Interfaces | 2x USB 2.0 |
| | 1x USB 3.0, Typ C |
| | 1x COM (RS-232/422/485) |
| Optional interfaces | Without optional interface |
| Network | 1 x Ethernet (10/100/1000 Mbps), RJ45 |
| Bus system | without bus system |

System properties

| | |
|---------------|------------|
| User software | QT browser |
|---------------|------------|

System requirements

| | |
|----------------|------------|
| Runtime system | Qt Browser |
|----------------|------------|

Electrical properties

| | |
|-------------------------|-------------------|
| Service life of battery | 5 years (typical) |
|-------------------------|-------------------|

1290801

<https://www.phoenixcontact.com/us/products/1290801>

Supply

| | |
|-----------------------------|---------------------|
| Supply voltage (DC) | 24 V DC \pm 20% |
| Supply voltage range | 18 V DC ... 32 V DC |
| Power supply unit | 24 V DC \pm 20 % |
| Max. current consumption | 1.81 A (24 V DC) |
| Typical current consumption | 0.79 A (24 V DC) |

Real-time clock

| | |
|----------------|----------------------|
| Realtime clock | Yes (battery-backed) |
|----------------|----------------------|

Mounting

| | |
|---------------|----------------|
| Mounting type | Front mounting |
|---------------|----------------|

Material specifications

| | |
|----------------------|------------------------------------|
| Color (Housing) | white aluminium (RAL 9006) |
| Material front plate | Aluminum (natural anodized) |
| Housing material | Aluminum cast alloy, powder-coated |

Connection data

| | |
|-----------------------------------|---|
| Connection method | Screw connection |
| Conductor cross-section, rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Stripping length | 7 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|-------------------------------|
| Degree of protection | IP66 (front), IP20 (back) |
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C |
| Permissible humidity (operation) | 5 % ... 85 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 85 % (non-condensing) |
| Shock | 15g with 11 ms impulse |
| Vibration (operation) | 1g |

Dimensions

External dimensions

| | |
|------------------------|---|
| Width / Height / Depth | 263 mm / 200 mm / 51 mm (Dimensions of the front plate) |
|------------------------|---|

Installation dimensions

| | |
|-------------------------------------|---|
| Width / Height / Installation depth | 252 mm / 189 mm / (Installation cutout) |
|-------------------------------------|---|

1290801

<https://www.phoenixcontact.com/us/products/1290801>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1290801>



IECEE CB Scheme
Approval ID: US-39088-UL



UL Listed
Approval ID: E238705



cUL Listed
Approval ID: E238705



IECEE CB Scheme
Approval ID: US-39088-UL



cUL Listed
Approval ID: E238705



UL Listed
Approval ID: E238705

1290801

<https://www.phoenixcontact.com/us/products/1290801>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27330201 |
| ECLASS-15.0 | 27330201 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001412 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43211900 |
|-------------|----------|

1290801

<https://www.phoenixcontact.com/us/products/1290801>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-15 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

EF3.1 Climate Change

| | |
|---------|-----------------|
| CO2e kg | 167.775 kg CO2e |
|---------|-----------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com