

# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply



1291193

<https://www.phoenixcontact.com/us/products/1291193>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i-Feed and input signal conditioner feeds 2-, 3- and 4-conductor measuring transducer and transmits 1:1 passive or active 0 mA / 4 mA ... 20 mA Ex i input signals as active non Ex i output signal. number of channels: 1, Standard configuration, 3-way isolation, Safety Integrity Level (SIL, IEC 61508): 3, Push-in connection

## Commercial data

Item number	1291193
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C430
Product key	DK121W
GTIN	4063151523664
Weight per piece (including packing)	194 g
Weight per piece (excluding packing)	160 g
Customs tariff number	85437090
Country of origin	DE

# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply



1291193

<https://www.phoenixcontact.com/us/products/1291193>

## Technical data

### Notes

Note on application	Accuracy, typically specified as a percentage of the measuring span (20 mA) at $U_N$ , 23°C
Notes on operation	Installation conditions influence the ambient temperature. Please refer to the "Control cabinet installation instructions".
Notes on operation	Output behavior = input signal

### Product properties

Product type	Repeater power supply
Product family	MACX Analog
No. of channels	1

### Electrical properties

Electrical isolation	3-way isolation
Electrical isolation between input and output	yes
Signal transmission behavior	In = Out
Temperature coefficient, typical	$\leq 0.05\%$ (10 K)
Reverse polarity protection	yes

#### Electrical isolation Input/output IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V <sub>PP</sub>

#### Electrical isolation Input/power supply IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V <sub>PP</sub>

#### Electrical isolation Input/error message output IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V <sub>PP</sub>

#### Electrical isolation Input 1 / input 2 IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V <sub>PP</sub>

#### Electrical isolation Output/supply

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

#### Electrical isolation Output 1/output 2

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

#### Electrical isolation Output/supply/error message output

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

### Supply

Nominal supply voltage	24 V DC
------------------------	---------

# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply



1291193

<https://www.phoenixcontact.com/us/products/1291193>

Supply voltage range	18 V ... 31.2 V
Power dissipation	2.2 W ( $R_L$ 250 $\Omega$ )
Power consumption	2.7 W (20 mA)

## Input data

Signal: Repeater power supply operation

Description of the input	active and passive current input, intrinsically safe
Input signal	Current
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA (with HART)
	0 mA ... 24 mA (Function area)
Input resistance current input	$\leq 100 \Omega$ (for mA sources)
Input current	$\leq 50$ mA (for mA sources)
Short-circuit current	$\leq 35$ mA
Line fault detection	< 3.6 mA (Line break)
	> 20.5 mA (Short circuit)
Open-circuit voltage	$\leq 26$ V

Signal: Signal conditioner operation

Description of the input	Passive current input, intrinsically safe
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA (with HART)
	0 mA ... 24 mA (Function area)
Input resistance current input	$\leq 100 \Omega$ (for mA sources)
Input current	$\leq 50$ mA
Short-circuit current	$\leq 35$ mA
Line fault detection	< 3.6 mA (Line break)
	> 20.5 mA (Short circuit)
Open-circuit voltage	$\leq 26$ V

## Output data

Signal: Error message output

Maximum switching voltage	30 V
Max. switching current	100 mA

Signal: Repeater power supply operation

Output description	Current output (active)
Current output signal	0 mA ... 20 mA
	4 mA ... 20 mA (with HART)
	0 mA ... 24 mA (Function area)
Load	0 $\Omega$ ... 600 $\Omega$
	0 $\Omega$ ... 379 $\Omega$ (with internal 221 $\Omega$ resistance for HART)
Output ripple (current)	$\leq 40 \mu\text{A}$ (effective)
Line fault detection	< 3.6 mA (Line break)

# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply



1291193

<https://www.phoenixcontact.com/us/products/1291193>

Signal: Signal conditioner operation

Output description	Signal conditioner operation
Current output signal	0 mA ... 20 mA
	4 mA ... 20 mA (with HART)
	0 mA ... 24 mA (Function area)
Load	0 Ω ... 600 Ω
	0 Ω ... 379 Ω (with internal 221 Ω resistance for HART)
Output ripple (current)	≤ 40 μA (effective)

## Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16

## Ex data

Ex installation (EPL)	Gc
Ex i circuits (EPL)	[Ga]
	[Da]
	[Ma]

Safety data: Repeater power supply operation

Max. internal inductance $L_i$	negligible
Max. internal capacitance $C_i$	negligible
Max. output voltage $U_o$	27 V
Max. output current $I_o$	88 mA
Max. output power $P_o$	576 mW
Safety-related maximum voltage $U_m$	253 V AC
IIA (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	28 mH / 2330 nF
IIB/IIIC (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	17 mH / 705 nF
IIC (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	2.3 mH / 90 nF
I (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	40 mH / 3750 nF
IIA (mixed circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	28 mH / 410 nF, 2 mH / 480 nF, 1 mH / 540 nF, 0.2 mH / 820 nF
IIB/IIIC (mixed circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	17 mH / 290 nF, 2 mH / 320 nF, 0.5 mH / 460 nF, 0.2 mH / 600 nF
IIC (mixed circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	2 mH / 42 nF, 1 mH / 56 nF, 0.5 mH / 72 nF, 0.2 mH / 90 nF
I (mixed circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	40 mH / 480 nF, 20 mH / 660 nF, 0.5 mH / 810 nF, 0.1 mH / 1200 nF

Safety data: Signal conditioner operation

# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply



1291193

<https://www.phoenixcontact.com/us/products/1291193>

Note	With connection of power sources
Input voltage $U_i$	30 V
Input current $I_i$	100 mA
Input power $P_i$	limited internally
Max. internal inductance $L_i$	negligible
Max. internal capacitance $C_i$	negligible
Max. output voltage $U_o$	4.1 V
Safety-related maximum voltage $U_m$	253 V AC

## Interfaces

### Data communication (bypass)

Protocols supported	HART-transparent
Frequency measuring range	0.5 kHz ... 10 kHz (bidirectional HART transmission)

## Signaling

Status display	Green LED (supply voltage)
	Red LED (line errors)

## Dimensions

Dimensional drawing	
Width	17.5 mm
Height	107.8 mm
Depth	113.7 mm
Depth NS 35/7,5	114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715)

## Material specifications

Flammability rating according to UL 94	V0
Housing material	PA 6.6

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20 (Terminal blocks)
	IP30 (Housing)
Ambient temperature (operation)	-20 °C ... 70 °C (Stand-alone device: any mounting position)
	-20 °C ... 55 °C (Group assembly: vertical DIN rail without circulating air)
	-20 °C ... 65 °C (Group assembly: vertical DIN rail with circulating air)

# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply



1291193

<https://www.phoenixcontact.com/us/products/1291193>

	-20 °C ... 60 °C (Group assembly: horizontal DIN rail without circulating air)
	-20 °C ... 65 °C (Group assembly: horizontal DIN rail with circulating air)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	≤ 95 % (non-condensing)

## Approvals

### ATEX

Identification	⊕ II (1) G [Ex ia Ga] IIC
	⊕ II (1) D [Ex ia Da] IIIC
	⊕ II 3 (1) G Ex nA nC [ia Ga] IIC T4 Gc
	⊕ I (M1) [Ex ia Ma] I

### IECEX

Identification	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex nA nC [ia Ga] IIC T4 Gc
	[Ex ia Ma] I

### Safety Integrity Level (SIL, IEC 61508)

Identification	3
----------------	---

## EMC data

Electromagnetic compatibility	Tested in accordance with the following standards and regulations: EN 61326-1 For industrial use, NAMUR NE 21
-------------------------------	---

## Standards and regulations

Electrical isolation	3-way isolation
----------------------	-----------------

## Mounting

Mounting type	NS 35/15, NS 35/7,5
Mounting position	vertical, horizontal

# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply




1291193

<https://www.phoenixcontact.com/us/products/1291193>

## Drawings

Dimensional drawing




# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply

1291193

<https://www.phoenixcontact.com/us/products/1291193>

Block diagram



# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply



1291193

<https://www.phoenixcontact.com/us/products/1291193>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1291193>

### Functional Safety

Approval ID: 22/05-248 R029 V1R0



### IECEX

Approval ID: IECEX BVS 21.0019X



### ATEX

Approval ID: BVS 21 ATEX E 017X

# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply



1291193

<https://www.phoenixcontact.com/us/products/1291193>

## Classifications

### ECLASS

ECLASS-13.0	27210120
ECLASS-15.0	27210120
ECLASS-15.0 ASSET	27250101

### ETIM

ETIM 10.0	EC002653
-----------	----------

### UNSPSC

UNSPSC 21.0	39121000
-------------	----------

# MACX MCR-EX-AP-RPSS-I-I-SP - Repeater power supply



1291193

<https://www.phoenixcontact.com/us/products/1291193>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b28b4445-7985-49e4-858c-6d4f0542c357

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)