

FIL-1S-1-20A-230AC-PT - EMC filter



1292316

<https://www.phoenixcontact.com/us/products/1292316>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



EMC filter (mains filter) for single-phase AC and DC systems (nominal voltage: up to 230 V AC, up to 220 V DC), for mounting on NS 35, nominal current: 20 A

Your advantages

- Reliable protection of sensitive equipment against high-frequency conducted interference
- Effective attenuation with current-coupled coils and X and Y capacitors
- Versatile in use with universal circuit design
- Improved filter effect with additional PE terminals, for connection to the local protective bonding
- User-friendly handling thanks to easy assembly and installation with Push-in connection technology (PT)

Commercial data

Item number	1292316
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL28
Product key	CLC151
GTIN	4063151524968
Weight per piece (including packing)	237 g
Weight per piece (excluding packing)	230 g
Customs tariff number	85480090
Country of origin	CN

FIL-1S-1-20A-230AC-PT - EMC filter



1292316

<https://www.phoenixcontact.com/us/products/1292316>

Technical data

Product properties

Product type	EMC filters
Type	DIN rail module, one-piece
Number of positions	2


Electrical properties

Nominal frequency f_N	50 Hz (60 Hz)
Nominal voltage U_N	230 V AC (TN-S/TT)
	230 V AC (IT, L-L)
	120 V AC (TN-S/TT)
	120 V AC (IT, L-L)
	220 V DC
Rated voltage (U_R)	250 V AC
	250 V DC

Connection data

Connection method	Push-in connection
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 14 (flexible)
	24 ... 12 (solid)

Dimensions

Dimensional drawing	
Width	45 mm
Height	99 mm
Depth	99.5 mm

Material specifications

Color	gray (RAL 7042)
	light gray (RAL 7035)
Flammability rating according to UL 94	V-0
Housing material	PC-GF10

Mechanical properties

Mechanical data

FIL-1S-1-20A-230AC-PT - EMC filter



1292316

<https://www.phoenixcontact.com/us/products/1292316>

Open side panel	No
-----------------	----

Protective circuit

Nominal voltage U_N	230 V AC (TN-S/TT)
	230 V AC (IT, L-L)
	120 V AC (TN-S/TT)
	120 V AC (IT, L-L)
	220 V DC
Nominal frequency f_N	50 Hz (60 Hz)
Rated current	20 A (50 °C)
Protective conductor current I_{PE}	≤ 0.2 mA
Input attenuation aE, sym.	> 65 dB (50 Ω / 1 MHz)
Input attenuation aE, asym.	> 20 dB (50 Ω / 1 MHz)
Capacity	2x 470 nF (X2)
	2x 2.2 nF (Y2)
Inductivity in series	2x 2.5 mH (with current compensation)
Short-circuit current rating I_{SCCR}	10 kA AC (gG, Class J)
	3 kA AC (MCB B)
	3 kA AC (MCB, UL 489 Tripping Curve Z or B)
	3 kA AC (MCB, CSA C22.2 No. 5-02 Tripping Curve Z or B)
	6 kA DC (gG, Class J)
Max. required back-up fuse	20 A AC/DC (gG, Class J)
	20 A AC (MCB B)
	20 A AC (MCB, UL 489 Tripping Curve Z or B)
	20 A AC (MCB, CSA C22.2 No. 5-02 Tripping Curve Z or B)

Filter data

Discharge resistance	940 k Ω
----------------------	----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C (dependent on the derating curve)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 70 °C
Altitude	≤ 2000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	15g (Half-sine / 11 ms / 3x $\pm X$, $\pm Y$, $\pm Z$)
Vibration (operation)	DNVGL-CG-0339 class A

Standards and regulations

Standards/specifications	IEC 60939-1
Standards/specifications	EN 60939-1
Standards/specifications	IEC 60939-2

FIL-1S-1-20A-230AC-PT - EMC filter



1292316

<https://www.phoenixcontact.com/us/products/1292316>


Standards/specifications	EN 60939-2
Standards/specifications	UL 60939-3
Standards/specifications	UL 1283
Standards/specifications	UL 121201
Standards/specifications	CSA C22.2 No. 8-13
Standards/specifications	CSA C22.2 No. 213-17

Mounting


Mounting type	DIN rail: 35 mm
---------------	-----------------


Drawings

Dimensional drawing




Diagram





Circuit diagram



FIL-1S-1-20A-230AC-PT - EMC filter



1292316

<https://www.phoenixcontact.com/us/products/1292316>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1292316>



IECEE CB Scheme

Approval ID: DE1-66248



VDE Zeichengenehmigung

Approval ID: 40054877



cUL Recognized

Approval ID: FILE E 526585



UL Recognized

Approval ID: FILE E 526585

CCA

Approval ID: DE1-34877-A1



DNV GL

Approval ID: TAA0000384



CSA

Approval ID: 80228707



CSAus

Approval ID: 80228707



cULus Recognized

Approval ID: E118989



cUL Recognized

Approval ID: FILE E 532830



UL Recognized

Approval ID: FILE E 532830

FIL-1S-1-20A-230AC-PT - EMC filter



1292316

<https://www.phoenixcontact.com/us/products/1292316>



cUL Recognized
Approval ID: E340736



UL Recognized
Approval ID: E340736



CSA
Approval ID: 80228706



CSAus
Approval ID: 80228706

FIL-1S-1-20A-230AC-PT - EMC filter



1292316

<https://www.phoenixcontact.com/us/products/1292316>

Classifications

ECLASS

ECLASS-13.0	27420208
ECLASS-15.0	27420290

ETIM

ETIM 10.0	EC002564
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

FIL-1S-1-20A-230AC-PT - EMC filter



1292316

<https://www.phoenixcontact.com/us/products/1292316>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com