

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular RJ45 PCB connectors, 1x1 single-port, connection direction of the connector to the PCB: 180 °, Shielded, number of positions: 8, 10 Gbps, PoE++, THT-THR, THD, Reflow, IP20, type of packaging: Tape and Reel

## Your advantages

- The right version for every application. Available with and without LED, single- and multi-port
- The reflow capability enables efficient, cost-optimized processing
- High standoffs allow ideal thermal airflow during processing
- Tape-on-reel packaging is perfect for automated processing
- The extended temperature range from -50 °C ... +85 °C enables use in demanding applications
- Through-hole technology (THT) provides high mechanical stability when connecting the female connector to the PCB

## Commercial data

Item number	1337238
Packing unit	120 pc
Minimum order quantity	120 pc
Sales key	AB12
Product key	ABNADA
GTIN	4063151638436
Weight per piece (including packing)	7.41 g
Weight per piece (excluding packing)	7.34 g
Customs tariff number	85366930
Country of origin	CN

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Technical data

### Product properties

Slots	1x1 single-port
Orientation to PCB	180.00 °
Type	THD
Number of positions	8 (8P8C)
Type of locking	Snap-in locking
Shielding	Shielded
Processing notes	Reflow
Type of packaging	Tape and Reel
Transmission speed	10 Gbps
Power transmission	PoE++ (according to IEEE 802.3bt)
Power PSE	90 W (Class 8 in accordance with IEEE 802.3bt)
Power PD	71 W (Class 4 in accordance with IEEE 802.3bt)

### Electrical properties

Pollution degree	2
Overvoltage category	I (IEC 60664-1)
Rated voltage	72 V DC
Rated surge voltage	1.5 kV DC (IEC 60664-1)
Rated current	1.5 A (IEC 60603-7)
Insulation resistance	> 500 M $\Omega$ (IEC 60603-7)
Test voltage (Contact/contact)	1.5 kV DC (IEC 60603-7)
Test voltage (Contact/shield)	1.5 kV DC (IEC 60603-7)

### Dimensions

Length	13.6 mm
Width	16.8 mm
Height	19 mm
Installed height	15.90 mm
Data pin length	2.00 mm

### Material specifications

Material Contact carrier	LCP
Flame resistance	UL 94 V0
Halogen-free	yes
Material Housing	Stainless steel
Material Housing pin coating (top layer/selective)	Sn
Material Contact	Phosphor bronze
Material Solder contact coating (intermediate layer)	Ni (1.27 $\mu$ m/50 $\mu$ "")
Material Solder contact coating (top layer/selective)	Sn (2.54 $\mu$ m / 100 $\mu$ "")
Material Plug contact coating (top layer/selective)	Au (1.27 $\mu$ m/50 $\mu$ "")

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

Material Plug contact coating (intermediate layer)	Ni (1.27 µm/50 µ")
--	--------------------

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 750 (IEC 60603-7)
Insertion force	< 20 N (IEC 60603-7)
Withdrawal force	< 20 N (IEC 60603-7)

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-50 °C ... 85 °C
Ambient temperature (storage/transport)	-50 °C ... 85 °C
Degree of protection (plugged in)	IP20 (IEC 60603-7)
Degree of protection (Not plugged in)	IP20 (IEC 60603-7)

### Test specification for vibration - sine

Acceleration	50 m/s <sup>2</sup>
Amplitude	0.35 mm
Sweep speed	1 octave/min

## Mounting

### Processing notes

Mounting type	THT-THR
Moisture Sensitive Level	MSL 1 (IEC 60068-2-58)
Solder cycles in the reflow	3 (IEC 60068-2-58)

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Drawings

Diagram



Classification reflow soldering profile

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1337238>



**UL Recognized**

Approval ID: FILE E 335024

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Classifications

### ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

### ETIM

ETIM 10.0	EC002637
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CUC-SP-J1ST-S/R4LT-THR - Modular RJ45 PCB connectors



1337238

<https://www.phoenixcontact.com/us/products/1337238>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)