

FL SWITCH 4800E-P5B - Power module



1312448

<https://www.phoenixcontact.com/us/products/1312448>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Modular power supply for FL SWITCH 48... managed switches. Wide input voltage range 90 V,AC to 264 V AC and 88 V DC to 300 V DC.



Your advantages

- Network structure according to IEC 61850
- IEEE 1613

Commercial data

Item number	1312448
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN17
Product key	DNN125
GTIN	4063151568153
Weight per piece (including packing)	1,044.5 g
Weight per piece (excluding packing)	745 g
Customs tariff number	85176200
Country of origin	TW

FL SWITCH 4800E-P5B - Power module



1312448

<https://www.phoenixcontact.com/us/products/1312448>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Power module
--------------	--------------

Input data

Input voltage	115 V AC
	230 V AC
	110 V DC
	250 V DC
Nominal input voltage range	90 V AC ... 264 V AC
	88 V DC ... 300 V DC
Input voltage range AC	90 V AC ... 264 V AC
Input voltage range DC	88 V DC ... 300 V DC
AC frequency range	50 Hz ... 60 Hz

Connection data

Input

Connection method	Screw connection
Conductor cross-section, rigid min.	0.8 mm ²
Conductor cross-section, rigid max.	6 mm ²
Conductor cross-section flexible min.	0.8 mm ²
Conductor cross-section flexible max.	6 mm ²
Conductor cross-section AWG min.	18
Conductor cross-section AWG max.	10

Dimensions

Width	151 mm
Height	40 mm
Depth	214 mm

Material specifications

Housing material	Steel
------------------	-------

Environmental and real-life conditions

FL SWITCH 4800E-P5B - Power module



1312448

<https://www.phoenixcontact.com/us/products/1312448>

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

Standards and regulations

Standards/specifications	IEC 61850
--------------------------	-----------

Mounting

Mounting type	Rack mounting (with holder)
Holder system	19" rack

FL SWITCH 4800E-P5B - Power module



1312448

<https://www.phoenixcontact.com/us/products/1312448>

Classifications

ECLASS

ECLASS-13.0	27040701
ECLASS-15.0	27040701

ETIM

ETIM 10.0	EC002540
-----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

FL SWITCH 4800E-P5B - Power module



1312448

<https://www.phoenixcontact.com/us/products/1312448>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com