

LS-EMLP (85,6X27) SR R3 - Device marker



1322596

<https://www.phoenixcontact.com/us/products/1322596>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Sheet, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 12



Your advantages

- Stick-on equipment marking with corner radius
- Prefabricated device markers in the proven laser-sheet format for ideal positioning in the marking device
- High contrast due to the silver top layer with black marking
- The corner radius makes the device markers particularly suitable for adhering to marker carriers and to actuator housings with recessed marking areas

Commercial data

Item number	1322596
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG241D
GTIN	4063151610722
Weight per piece (including packing)	38.8 g
Weight per piece (excluding packing)	38 g
Country of origin	DE

LS-EMLP (85,6X27) SR R3 - Device marker



1322596

<https://www.phoenixcontact.com/us/products/1322596>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	12
Identification technology	Direct laser marking

Dimensions

Width	85.60 mm
Height	27.00 mm
Depth	0.85 mm

Material specifications

Color	silver-colored
Material	ABS
Base element material	ABS
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 85 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

LS-EMLP (85,6X27) SR R3 - Device marker



1322596

<https://www.phoenixcontact.com/us/products/1322596>

Mounting type	adhesive
---------------	----------

LS-EMLP (85,6X27) SR R3 - Device marker



1322596

<https://www.phoenixcontact.com/us/products/1322596>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

LS-EMLP (85,6X27) SR R3 - Device marker



1322596

<https://www.phoenixcontact.com/us/products/1322596>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com