

NBC-COX-CNM/5.0-M/COX-CKM - Coaxial cable



1340147

<https://www.phoenixcontact.com/us/products/1340147>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coaxial cable, 50 Ω , length: 5 m, N(m) - SMA(m), external cable diameter: 4.9 mm, transmission frequency: ≤ 7.25 GHz, typical attenuation: 800 MHz 2.3 dB, 2.4 GHz 3.8 dB, 5.8 GHz 6 dB, 7.25 GHz 7.3 dB

Your advantages

- Future-proof, thanks to the use of lead-free materials
- Ideal for WLAN, Bluetooth, LTE, and 5G signals
- The frequency range up to 7.25 GHz enables the use of high Wi-Fi 6 and 5G frequency bands
- Use of UV-resistant LSZH cable enables use in virtually all industrial field communication applications

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1340147 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB14 |
| Product key | DNC6Z4 |
| GTIN | 4063151645496 |
| Weight per piece (including packing) | 227.2 g |
| Weight per piece (excluding packing) | 233 g |
| Customs tariff number | 85442000 |
| Country of origin | DE |

1340147

<https://www.phoenixcontact.com/us/products/1340147>

Technical data

Product properties

| | |
|---------------------|---------------|
| Product type | Coaxial cable |
| Type | Coaxial |
| Number of positions | 1 |
| Type of packaging | PE bag |
| Shielded | yes |
| Cable outlet | straight |

Electrical properties

| | |
|---------------------------|--------------------------|
| Rated surge voltage | 1 kV _{rms} (AC) |
| Frequency range | 0.1 GHz ... 7.25 GHz |
| Insulation resistance | ≥ 5 GΩ |
| Wave impedance | 50 Ω |
| Max. conductor resistance | 23 Ω/km |

Connection data

| | |
|-------------------|----------------|
| Tightening torque | 0.7 ... 1.1 Nm |
|-------------------|----------------|

Material specifications

| | |
|--|--------|
| Flammability rating according to UL 94 | ja |
| Conductor material | Copper |

Connector

Connection 1

| | |
|--------------|---------------------------|
| Type | Plug straight Coaxial N |
| Locking type | Screw locking mechanism |
| Shielded | yes |
| Material | Copper alloy (Housing) |
| | CuSnZn3 (Housing surface) |
| | Silicon (O-ring) |
| | Copper alloy (Contact) |
| | Cu2Ag5 (Contact surface) |
| | PTFE (Insulation) |

Connection 2

| | |
|--------------|---------------------------|
| Type | Plug straight Coaxial SMA |
| Locking type | Screw locking mechanism |
| Shielded | yes |
| Material | Copper alloy (Housing) |
| | NiP-Au (Housing surface) |
| | Silicon (O-ring) |
| | Copper alloy (Contact) |

NBC-COX-CNM/5.0-M/COX-CKM - Coaxial cable



1340147

<https://www.phoenixcontact.com/us/products/1340147>

| | |
|--|--------------------------|
| | NiP-Au (Contact surface) |
| | PTFE (Insulation) |

Cable/line

| | |
|--------------|--------|
| Cable length | 5.00 m |
|--------------|--------|

Coaxial, 4.9 mm, FRNC, 50 Ω [Koaxial]

| | |
|---------------------------|-----------------------------|
| Cable type | Coaxial, 4.9 mm, FRNC, 50 Ω |
| Cable type (abbreviation) | Koaxial |
| External cable diameter | 4.90 mm |
| Outer sheath, material | FRNC |
| External sheath, color | black |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------------------|
| Insertion/withdrawal cycles | > 100 |
| Smallest bending radius | 4x cable diameter |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Ambient temperature (assembly) | -5 °C ... 55 °C |
| Resistance to UV radiation | yes |

Standards and regulations

| | |
|------------------|-----|
| Flame resistance | yes |
|------------------|-----|

Flame retardancy

| | |
|--------------------------|------------------|
| Standard designation | Flame retardancy |
| Standards/specifications | IEC 60332-3-24 |

Halogen-free

| | |
|--------------------------|--------------|
| Standard designation | Halogen-free |
| Standards/specifications | IEC 60754-2 |

UL

| | |
|--------------------------|-------------------------|
| Standard designation | AWM Style |
| Standards/specifications | UL 1375 |
| Note | 80 °C / 30 V |
| Standard designation | HF connector |
| Standards/specifications | IEC 61169-16 |
| Note | Pin connector pattern N |
| Standard designation | HF connector |
| Standards/specifications | IEC 61169-15 |

NBC-COX-CNM/5.0-M/COX-CKM - Coaxial cable



1340147

<https://www.phoenixcontact.com/us/products/1340147>

| Note | |
|------|--|
|------|--|

| | |
|--|---------------------------|
| | Pin connector pattern SMA |
|--|---------------------------|

NBC-COX-CNM/5.0-M/COX-CKM - Coaxial cable



1340147

<https://www.phoenixcontact.com/us/products/1340147>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060310 |
| ECLASS-15.0 | 27060310 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001682 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

1340147

<https://www.phoenixcontact.com/us/products/1340147>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 7.658 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com