CRIMPFOX-TC HC 4/DIE - Replacement die

1324130

https://www.phoenixcontact.com/us/products/1324130

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Replacement die for CRIMPFOX-TC HC 4, CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations

Your advantages

- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1324130
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Y
GTIN	4063151613723
Weight per piece (including packing)	48.52 g
Weight per piece (excluding packing)	48.1 g
Customs tariff number	82032000
Country of origin	SE

Technical data

Notes

Note on application	For 0.14 mm² ... 4.0 mm² solid crimp contacts from the CK1.6 ED..., CK2.5 ED..., CK4.0 ED... series, the packing slip includes a detailed list of the crimp contacts

Product properties

Product type	Die
Compression	Square crimp

Crimping position 1

Min. cross section	0.14 mm²
Max. cross section	1 mm²
AWG min	26
AWG max	18

Crimping position 2

Max. cross section	1.5 mm²
AWG max	16

Crimping position 3

Max. cross section	2.5 mm²
AWG max	14

Crimping position 4

Max. cross section	4 mm²
AWG max	12

Connection data

Conductor connection

Cross section range, metric	0.14 mm² ... 4 mm²
Cross section range AWG	26 ... 12

Dimensions

Width	11 mm
Height	35 mm
Length	32 mm

Material specifications

Color	black (RAL 9005)
Material	Steel

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1324130

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21043852
ECLASS-15.0	21043852

ETIM

ETIM 10.0	EC001282

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com