

# CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/us/products/1324130>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Replacement die for CRIMPFOX-TC HC 4, CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations

## Your advantages

- Marked die stations for precise processing of corresponding cross sections

## Commercial data

Item number	1324130
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH313Y
GTIN	4063151613723
Weight per piece (including packing)	48.52 g
Weight per piece (excluding packing)	48.1 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/us/products/1324130>

## Technical data

### Notes

Note on application	For 0.14 mm <sup>2</sup> ... 4.0 mm <sup>2</sup> solid crimp contacts from the CK1.6 ED..., CK2.5 ED..., CK4.0 ED... series, the packing slip includes a detailed list of the crimp contacts
---------------------	--

### Product properties

Product type	Die
Compression	Square crimp

#### Crimping position 1

Min. cross section	0.14 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
AWG min	26
AWG max	18

#### Crimping position 2

Max. cross section	1.5 mm <sup>2</sup>
AWG max	16

#### Crimping position 3

Max. cross section	2.5 mm <sup>2</sup>
AWG max	14

#### Crimping position 4

Max. cross section	4 mm <sup>2</sup>
AWG max	12

### Connection data

#### Conductor connection

Cross section range, metric	0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Cross section range AWG	26 ... 12

### Dimensions

Width	11 mm
Height	35 mm
Length	32 mm

### Material specifications

Color	black (RAL 9005)
Material	Steel

# CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/us/products/1324130>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1324130>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/us/products/1324130>

## Classifications

### ECLASS

ECLASS-13.0	21043852
ECLASS-15.0	21043852

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-TC HC 4/DIE - Replacement die



1324130

<https://www.phoenixcontact.com/us/products/1324130>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)