

CUC-COX-J1M-A/LFS - Coaxial PCB connector



1340150

<https://www.phoenixcontact.com/us/products/1340150>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coaxial PCB connector, degree of protection: IP20, number of positions: 1, 12 Gbps, material: Metal, connection method: Solder connection, cable outlet: straight

Your advantages

- Future-proof, thanks to the use of lead-free materials
- Complete documentation saves developers time during design-in
- Ideal for WLAN, Bluetooth, LTE, and 5G signals
- The reflow capability of PCB connectors enables efficient and cost-optimized processing
- Tape-on-reel packaging

Commercial data

Item number	1340150
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	AB14
Product key	ABNFBB
GTIN	4063151646431
Weight per piece (including packing)	6.11 g
Weight per piece (excluding packing)	6.1 g
Customs tariff number	85366910
Country of origin	DE

CUC-COX-J1M-A/LFS - Coaxial PCB connector



1340150

<https://www.phoenixcontact.com/us/products/1340150>

Technical data

Product properties

Product type	Data connector (device side)
Type	Coaxial
Number of positions	1
Connection profile	R-SMA (f)
Type of packaging	Tape and Reel
[W] tape width	32.00 mm
[A] coil diameter	330.00 mm
Cable outlet	straight
Thread type	1/4-36 UNS

Electrical properties

Rated surge voltage (III/2)	1500 V
Frequency range	10 Hz
Insulation resistance	5 GΩ
Test voltage	1000 V _{rms}
Transmission medium	Copper
Transmission speed	12.4 Gbps
Wave impedance	50 Ω
Max. conductor resistance	0.8 Ω/m

Output data

Transmission frequency	1.00 GHz
------------------------	----------

Connection data

Connection technology

Connection method	Solder connection
Locking mechanism tightening torque	1.10 Nm

Dimensions

Width	6.5 mm
Height	11.6 mm
Length	14.2 mm
Installed height	9.60 mm
Orientation to PCB	90.00 °

Material specifications

Material	Metal
Flammability rating according to UL 94	V0
Housing material	Metal
Contact material	CuBe2

CUC-COX-J1M-A/LFS - Coaxial PCB connector



1340150

<https://www.phoenixcontact.com/us/products/1340150>

Contact surface material	NiP-Au
--------------------------	--------

Cable/line

Cable resistance	0.8 Ω /m
Wave impedance	50 Ω
Halogen-free	no

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
Extraction force per signal contact	< 20 N
Locking mechanism tightening torque	1.10 Nm

Environmental and real-life conditions

Test specification

Specification	DIN EN 61169-1
Contact resistance R_2	2.00 m Ω
Insulation resistance, neighboring contacts	5 G Ω
Impulse withstand voltage at sea level	1400.00 V DC
Power-frequency withstand voltage	1000.00 V AC

Test specification

Specification	DIN EN 60068-2-14 Test Na
Cold stress	-10°C

Test specification

Specification	DIN EN 60068-2-6 Test Fc
Frequency	10-2000-10 Hz
Sweep speed	1 octave/min
Amplitude	0.75 mm
Acceleration	100.00 m/s ²
Test duration	2.50 h

Mounting

Processing notes

Process	THR
Moisture Sensitive Level	MSL 1

Drawings

Diagram



Classification reflow soldering profile

CUC-COX-J1M-A/LFS - Coaxial PCB connector



1340150

<https://www.phoenixcontact.com/us/products/1340150>

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 10.0	EC002637
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-COX-J1M-A/LFS - Coaxial PCB connector



1340150

<https://www.phoenixcontact.com/us/products/1340150>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com