D3PC-MP 0.50-1.25-F-SN-L - Crimp contact

1340363

https://www.phoenixcontact.com/us/products/1340363

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, nominal current: 6 A, contact surface: Tin, product range: D3PC-MP-F

Commercial data

Item number	1340363
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	AA02
Product key	AABCUB
GTIN	4063151646172
Weight per piece (including packing)	0.451 g
Weight per piece (excluding packing)	0.451 g
Customs tariff number	85366990
Country of origin	CN

Technical data

Product properties

Product type	Crimp contact
Product family	D3PC-MP-F

Connection data

Stripping length	4.5 mm
Conductor cross-section AWG	20 ... 16

Material specifications

Contact surface	Tin Sn
Contact surface material	Tin
Metal surface terminal point (top layer)	Tin (1 - 3 µm Sn)
Metal surface contact area (top layer)	Tin (1 - 3 µm Sn)
Surface characteristics	hot-dip tin-plated
Contact material	Cu alloy

Electrical properties

Nominal current I_N	6 A

Classifications

ECLASS

ECLASS-13.0	27460291
ECLASS-15.0	27460291

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com