

MC 1000-MM SC - FO converters



1329817

<https://www.phoenixcontact.com/us/products/1329817>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic converter with SC duplex connection (1310 nm) for 100Base-TX to multimode fiber optics, DIN rail mountable.

Product description

The MC 1000-MM SC media converter comes with one 10/100 Mbps twisted-pair RJ45 port and one 100 Mbps multimode fiber optics port with an SC-duplex connector

Your advantages

- Auto MDI/MDI-X switch-over
- Data transfer rates of 100 Mbps
- Link fault pass through (LFPT) function for easy connection monitoring
- Class 1 laser product complies with EN 60825-1

Commercial data

Item number	1329817
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN06
Product key	DNC314
GTIN	4063151624569
Weight per piece (including packing)	155.733 g
Weight per piece (excluding packing)	124 g
Customs tariff number	85176200
Country of origin	MY

MC 1000-MM SC - FO converters



1329817

<https://www.phoenixcontact.com/us/products/1329817>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Media converter
Product family	MC 1000
MTTF	84.6 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
	756.3 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	668.4 Years (Telcordia standard, temperature 25 °C, operating cycle 100 % (7 days a week, 24 hours a day))

Electrical properties

Maximum power dissipation for nominal condition	1.4 W
---	-------

Supply

Supply voltage range	12 V DC ... 48 V DC
Nominal supply voltage	24 V DC
Typical current consumption	59 mA (24 V DC)
Max. current consumption	170 mA (12 V DC, 60 °C)

Connection data

Supply

Connection method	Push-in spring connection
Single conductor/terminal point, rigid	0.2 mm² ... 2.5 mm²
Single-wire/terminal point, flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section, flexible [AWG]	24 ... 12
Conductor cross-section AWG	24 ... 12
Stripping length	10.00 mm

Interfaces

Signal	Ethernet
--------	----------

Data: optical FO

Transmit capacity, minimum	-20 dBm (62.5/125 µm, multimode fiberglass)
	-23.5 dBm (50/125 µm, multimode fiberglass)
Transmit capacity, maximum	-14 dBm

MC 1000-MM SC - FO converters



1329817

<https://www.phoenixcontact.com/us/products/1329817>

Transmission length incl. 3 dB system reserve	2 km
Connection method	SC duplex
Wavelength	1310 nm
Minimum receiver sensitivity	-32 dBm
Maximum receiver sensitivity	-8 dBm
Transmission medium	Multi-mode fiberglass

Data: Ethernet interface, 100Base-T(X) in accordance with IEEE 802.3

Transmission speed	10/100 Mbps
Connection method	RJ45 jack, shielded
No. of channels	1
Transmission length	100 m (twisted pair, shielded)
Transmission medium	Copper
Signal LEDs	LNK/ACT, SPD, US
Auto-negotiation modes	Auto
Link through	Link fault pass through
MDI-/MDI-X switchover	Auto-MDI(X)

Dimensions

Width	22.5 mm
Height	123 mm
Depth	90 mm

Material specifications

Color (Housing)	gray (RAL 7042)
Color (Cover)	light gray (RAL 7035)
Material (Housing)	Polyamide fiberglass reinforced

Cable/line

FO cable

Fiber types	50/125 µm
	62.5/125 µm
	Fiberglass

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Operation: 5g, 150 Hz, Criterion 3
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Operation: 30g, 11 ms half-sine shock pulse

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

MC 1000-MM SC - FO converters



1329817

<https://www.phoenixcontact.com/us/products/1329817>

Altitude	≤ 2000 m (in acc. with UL)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Shock	300 m/s ² , 11 ms (IEC 60068-2)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Comments	Criterion B
----------	-------------

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Electromagnetic HF field

Comments	Criterion A
----------	-------------

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Fast transients (burst)

Comments	Criterion A
----------	-------------

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Surge current load (surge)

Comments	Criterion B
----------	-------------

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

Comments	Criterion A
----------	-------------

Emitted interference

Standards/regulations	EN 55032
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715
Useable DIN rail type	DIN rail: 35 mm

MC 1000-MM SC - FO converters



1329817

<https://www.phoenixcontact.com/us/products/1329817>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1329817>



cULus Listed

Approval ID: E238705



IECEE CB Scheme

Approval ID: CA-11671-M1-UL

MC 1000-MM SC - FO converters



1329817

<https://www.phoenixcontact.com/us/products/1329817>

Classifications

ECLASS

ECLASS-13.0	19170411
ECLASS-15.0	19170411

ETIM

ETIM 10.0	EC001467
-----------	----------

UNSPSC

UNSPSC 21.0	43223323
-------------	----------

MC 1000-MM SC - FO converters



1329817

<https://www.phoenixcontact.com/us/products/1329817>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com