

# MC 1000T-MM LC - FO converters



1330259

<https://www.phoenixcontact.com/us/products/1330259>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fiber optic converter with LC duplex connection (1310 nm) for 100Base-TX to multimode fiber optics, DIN rail mountable, extended temperature range, redundant power supply.

## Product description

The MC 1000T-MM LC media converter comes with one 10/100 Mbps twisted-pair RJ45 port and one 100 Mbps multimode fiber optics port with an LC connector and wide temperature range.

## Your advantages

- Auto MDI/MDI-X switch-over
- Data transfer rates of 100 Mbps
- Link fault pass through (LFPT) function for easy connection monitoring
- Class 1 laser product complies with EN 60825-1

## Commercial data

Item number	1330259
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN06
Product key	DNC314
GTIN	4063151627003
Weight per piece (including packing)	273.9 g
Weight per piece (excluding packing)	180 g
Customs tariff number	85176200
Country of origin	MY

# MC 1000T-MM LC - FO converters



1330259

<https://www.phoenixcontact.com/us/products/1330259>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Media converter
Product family	MC 1000T
MTTF	68.5 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
	508.3 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	331.4 Years (Telcordia standard, temperature 25 °C, operating cycle 100 % (7 days a week, 24 hours a day))

### Electrical properties

Maximum power dissipation for nominal condition	1.5 W
---	-------

#### Supply

Supply voltage range	12 V DC ... 57 V DC
Nominal supply voltage	24 V DC
	48 V DC
Typical current consumption	62 mA (24 V DC)
Max. current consumption	170 mA (12 V DC, 75 °C)

### Output data

#### Signal

Voltage output signal	12 V DC ... 48 V DC (depending on the input voltage)
Current output signal	100 mA

### Connection data

#### Supply

Connection method	Push-in spring connection
Single conductor/terminal point, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Single-wire/terminal point, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	24 ... 12
Stripping length	10.00 mm

### Interfaces

# MC 1000T-MM LC - FO converters



1330259

<https://www.phoenixcontact.com/us/products/1330259>

Signal	Ethernet
--------	----------

## Data: optical FO

Transmit capacity, minimum	-20 dBm (62.5/125 µm, multimode fiberglass)
	-23.5 dBm (50/125 µm, multimode fiberglass)
Transmit capacity, maximum	-14 dBm
Transmission length incl. 3 dB system reserve	2 km
Connection method	LC duplex
Wavelength	1310 nm
Minimum receiver sensitivity	-31 dBm
Maximum receiver sensitivity	-8 dBm
Transmission medium	Multi-mode fiberglass

## Data: Ethernet interface, 100Base-T(X) in accordance with IEEE 802.3

Transmission speed	10/100 Mbps
Connection method	RJ45 jack, shielded
No. of channels	1
Transmission length	100 m (twisted pair, shielded)
Transmission medium	Copper
Signal LEDs	LNK/ACT, SPD, Err, US, US2
Auto-negotiation modes	Auto
Link through	Link fault pass through
MDI-/MDI-X switchover	Auto-MDI(X)

## Dimensions

Width	22.5 mm
Height	125 mm
Depth	90 mm

## Material specifications

Color (Housing)	gray (RAL 7042)
Color (Cover)	light gray (RAL 7035)
Material (Housing)	Polyamide fiberglass reinforced
	Aluminum
	Sheet steel DC01

## Cable/line

### FO cable

Fiber types	50/125 µm
	62.5/125 µm
	Fiberglass

## Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Operation: 5g, 150 Hz, Criterion 3
--	------------------------------------

# MC 1000T-MM LC - FO converters



1330259

<https://www.phoenixcontact.com/us/products/1330259>

Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Operation: 30g, 11 ms half-sine shock pulse
---	---

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m (in acc. with UL)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Shock	300 m/s <sup>2</sup> , 11 ms (IEC 60068-2)

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### UL, USA/Canada

Identification	Class I, Division 2, Groups A, B, C, and D, T4
----------------	--

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

### Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

### Electrostatic discharge

Comments	Criterion B
----------	-------------

### Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

### Electromagnetic HF field

Comments	Criterion A
----------	-------------

### Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

### Fast transients (burst)

Comments	Criterion A
----------	-------------

### Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

### Surge current load (surge)

Comments	Criterion B
----------	-------------

### Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

# MC 1000T-MM LC - FO converters



1330259

<https://www.phoenixcontact.com/us/products/1330259>

## Conducted interference

Comments	Criterion A
----------	-------------

## Emitted interference

Standards/regulations	EN 55032
-----------------------	----------

## Mounting

Mounting type	DIN rail mounting
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715
Useable DIN rail type	DIN rail: 35 mm

# MC 1000T-MM LC - FO converters



1330259

<https://www.phoenixcontact.com/us/products/1330259>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1330259>



**cULus Listed**

Approval ID: E238705

**BSH**

Approval ID: BSH Nr. 1176



**IECEE CB Scheme**

Approval ID: CA-11671-M1-UL

**DNV**

Approval ID: TAA00003RU



**cULus Listed**

Approval ID: E196811

# MC 1000T-MM LC - FO converters



1330259

<https://www.phoenixcontact.com/us/products/1330259>

## Classifications

### ECLASS

ECLASS-13.0	19170411
ECLASS-15.0	19170411

### ETIM

ETIM 10.0	EC001467
-----------	----------

### UNSPSC

UNSPSC 21.0	43223323
-------------	----------

# MC 1000T-MM LC - FO converters



1330259

<https://www.phoenixcontact.com/us/products/1330259>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)