

ME MAX 22,5-KIT-SF G 2-2-7035+4MSTBT4 - Housing set



1342905

<https://www.phoenixcontact.com/us/products/1342905>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, for mounting on a DIN rail, color: light gray (similar RAL 7035), width: 22.5 mm, height: 85 mm, depth: 69.55 mm, incl. 4 PCB connectors, 4-pos., screw connection, for 2.5 mm², nominal current: 12 A, 320 V, PCB surface: 2600 mm²

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1342905 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC08 |
| Product key | ACHABK |
| GTIN | 4063151657611 |
| Weight per piece (including packing) | 99.72 g |
| Weight per piece (excluding packing) | 99.72 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

ME MAX 22,5-KIT-SF G 2-2-7035+4MSTBT4 - Housing set

1342905

<https://www.phoenixcontact.com/us/products/1342905>

Set consists of

ME MAX 22,5 SF G 2-2 KMGY - Electronics housing

2869362

<https://www.phoenixcontact.com/us/products/2869362>



DIN rail housing, Complete housing with metal foot catch, ultra-flat design, without vents, width: 22.6 mm, height: 85 mm, depth: 69.55 mm, color: light gray (similar RAL 7035), cross connection: DIN rail bus connector (optional), number of positions cross connector: 5

ME BUS FE CONTACT - Functional ground contact

2278076

<https://www.phoenixcontact.com/us/products/2278076>



DIN rail housing, FE contact, width: 5 mm, height: 15.25 mm, depth: 9.5 mm

ME MAX 22,5-KIT-SF G 2-2-7035+4MSTBT4 - Housing set

1342905

<https://www.phoenixcontact.com/us/products/1342905>

MSTBO 2,5/ 4-G1L KMGY - PCB header

2907774

<https://www.phoenixcontact.com/us/products/2907774>



PCB headers, nominal cross section: 2.5 mm², color: light gray, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Pin, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: MSTBO 2,5/...-G1L, pitch: 5 mm, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.5 mm, number of solder pins per potential: 1, Pin connector pattern alignment: Orthogonal, locking: without, type of packaging: packed in cardboard, Product with pin output on left side

MSTBO 2,5/ 4-G1R KMGY - PCB header

2907787

<https://www.phoenixcontact.com/us/products/2907787>



PCB headers, nominal cross section: 2.5 mm², color: light gray, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Pin, number of rows: 1, number of positions: 4, product range: MSTBO 2,5/...-G1R, mounting: Wave soldering, number of solder pins per potential: 1, Pin connector pattern alignment: Orthogonal, locking: without, Product with pin output on right side

ME MAX 22,5-KIT-SF G 2-2-7035+4MSTBT4 - Housing set

1342905

<https://www.phoenixcontact.com/us/products/1342905>

MSTBT 2,5 HC/ 4-STP GY7035 - PCB connector

2200332

<https://www.phoenixcontact.com/us/products/2200332>



PCB connector, nominal cross section: 2.5 mm², color: light gray, nominal current: 16 A (see derating curve), rated voltage (III/2): 320 V, contact surface: Sn, contact connection type: Socket, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: MSTBT 2,5 HC/...-STP, pitch: 5 mm, connection method: Screw connection with tension sleeve, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON MSTB 2,5 advanced, locking: without, mounting method: without, type of packaging: packed in cardboard

ME MAX 22,5-KIT-SF G 2-2-7035+4MSTBT4 - Housing set



1342905

<https://www.phoenixcontact.com/us/products/1342905>

Technical data

Notes

| | |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Assembly note | Please observe the assembly instructions available in the download area. |
| Recommendation | Material of contact pads for bus connector, galvanic gold (hard gold) |
| General | The PCB surface specification is for orientation purposes and is based on a basic PCB. The housing can also accommodate several PCBs. |


Product properties

| | |
|-----------------------------------|-----------------------|
| Product type | Stackable housing set |
| Housing type | DIN rail housing |
| Housing series | ME-MAX |
| Number of positions | 16 |
| Max. number of positions | 16 (pitch: 5 mm) |
| Number of rows | 2 |
| Ventilation openings present | yes |
| Anzahl der Etagen Housing (Makro) | 2 (Both sides) |

Connection data

| | |
|-------------------|--------------------------------------|
| Connection method | Screw connection with tension sleeve |
|-------------------|--------------------------------------|

Dimensions

| | |
|---------------------------------|-------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width | 22.5 mm |
| Height | 85 mm |
| Depth | 69.55 mm |
| Depth from top edge of DIN rail | 62.9 mm |

PCB design

| | |
|---------------|-------------------|
| PCB thickness | 1.4 mm ... 1.8 mm |
|---------------|-------------------|

Material specifications

| | |
|----------------------------------------|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

ME MAX 22,5-KIT-SF G 2-2-7035+4MSTBT4 - Housing set



1342905

<https://www.phoenixcontact.com/us/products/1342905>

Environmental and real-life conditions

Ambient conditions

| | |
|-----------------------------------------|----------------------------------------------------|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % (maximum) |

PCB data

| | |
|-----------------------|----------------------|
| Number of PCB holders | 1 |
| Type of PCB mount | Latching |
| Total PCB surface | 2600 mm ² |
| Thickness of the PCB | 1.4 mm ... 1.8 mm |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Packaging specifications

| | |
|----------------------|---------------------|
| Type of packaging | packed in cardboard |
| Outer packaging type | Carton |


ME MAX 22,5-KIT-SF G 2-2-7035+4MSTBT4 - Housing set

1342905

<https://www.phoenixcontact.com/us/products/1342905>

Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.

ME MAX 22,5-KIT-SF G 2-2-7035+4MSTBT4 - Housing set



1342905

<https://www.phoenixcontact.com/us/products/1342905>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190301 |
| ECLASS-15.0 | 27190301 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001031 |
|----------|----------|

ME MAX 22,5-KIT-SF G 2-2-7035+4MSTBT4 - Housing set



1342905

<https://www.phoenixcontact.com/us/products/1342905>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.486 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com