

# NBC-USB2.0-UAM/2,0-PVC/UAM - USB cable



1333139

<https://www.phoenixcontact.com/us/products/1333139>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



USB cable, design: USB-A, degree of protection: IP20, cable length: 2 m, number of positions: 4, 480 Mbps, cable outlet: straight, USB 2.0

## Your advantages

- Data transmission up to 480 Mbps
- Reliable data transmission thanks to 100 % testing

## Commercial data

Item number	1333139
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB14
Product key	ABNDBA
GTIN	4063151631024
Weight per piece (including packing)	81.2 g
Weight per piece (excluding packing)	81.2 g
Customs tariff number	85444290
Country of origin	CN

# NBC-USB2.0-UAM/2,0-PVC/UAM - USB cable



1333139

<https://www.phoenixcontact.com/us/products/1333139>

## Technical data

### Product properties

Product type	Data cable preassembled
Type	USB-A
Sensor type	USB 2.0
Number of positions	4
Connection profile	USB-A
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Interfaces

Transmission speed	480 Mbps
--------------------	----------

### Electrical properties

Rated current	1.5 A
Insulation resistance	10 MΩ
Test voltage	300 V AC
	300 V AC
Test voltage Core/Core	300 V AC
Test voltage Core/Shield	300.00 V AC
Transmission speed	480 Mbps
Transmission characteristics (category)	USB 2.0
Transmission speed	480 Mbps

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	> 1500
Insertion force per signal contact	< 35.00 N
Extraction force per signal contact	< 10 N
Max. bending cycles	100
Smallest bending radius	3,7xD

### Material specifications

Color of the housing part	black
Outer sheath, material	PVC
Conductor material	Cu

### Dimensions

Width	15.8 mm
-------	---------

# NBC-USB2.0-UAM/2,0-PVC/UAM - USB cable



1333139

<https://www.phoenixcontact.com/us/products/1333139>

Height	8 mm
Length	45 mm

## Connector

### Connection 1

Type	Plug straight USB type A
Shielded	yes
Insertion/withdrawal cycles	1500
Insulation resistance	10 M $\Omega$
Overvoltage category	I
Degree of pollution	2
Degree of protection	IP20

### Connection 2

Type	Plug straight USB type A
Shielded	yes
Insertion/withdrawal cycles	1500
Insulation resistance	10 M $\Omega$
Degree of pollution	2
Degree of protection	IP20

## Cable/line

Cable length	2.00 m
--------------	--------

### PVC USB 2.0 black [USB]

Shielded	yes
Cable type	PVC USB 2.0 black
Cable type (abbreviation)	USB
External cable diameter	5.50 mm
Outer sheath, material	PVC
External sheath, color	black
Shielding	Aluminum-lined foil

## Environmental and real-life conditions

### Test specification

Cold stress	-40 °C/96 h
Thermal stress	85 °C/96 h
Corrosive stress	Salt spray test UL364-26
Insulation resistance, neighboring contacts	10 M $\Omega$

# NBC-USB2.0-UAM/2,0-PVC/UAM - USB cable



1333139

<https://www.phoenixcontact.com/us/products/1333139>

## Classifications

### ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060328

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# NBC-USB2.0-UAM/2,0-PVC/UAM - USB cable



1333139

<https://www.phoenixcontact.com/us/products/1333139>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)