

VIP-PA/20XOE/1,0M/FB3000 - Front adapter



1360225

<https://www.phoenixcontact.com/us/products/1360225>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VIP power cabling, universal front adapter with assembled shielded round cable for connection to 20-pos. Emerson FB3000 3MSG12 I/O modules. 1 x 20 single wires (each ferruled and marked) can be connected (field connection, e.g., via 20 terminal blocks).

Commercial data

Item number	1360225
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C423
Product key	DK2BNK
GTIN	4063151689995
Weight per piece (excluding packing)	177.6 g
Customs tariff number	85444290
Country of origin	MX

1360225

<https://www.phoenixcontact.com/us/products/1360225>

Technical data

Product properties

Product type	Front adapter
--------------	---------------

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (DC)	≤ 31 V DC
Current (per branch)	≤ 0.5 A

Supported controller: Emerson FB3000

Suitable I/O card	3MSG12
	3HTSG4
	3OTSG8
	3DIS16
	3DOS16
	3MSG6
	3MSG8

Connection data

Controller level

Connection method	Plug-in connection
Note	Can be plugged onto 12-ch. "3MSG12" I/O modules

Field level

Connection method	Single wires
Number of connections	20
Number of positions	1
Note	The wires are marked and fitted with ferrules

Dimensions

Cable

Length	1 m
--------	-----

Cable/line

Number of positions	20
Shielded	yes
Conductor type	Assembled shielded round cable
AWG signal line	22
Conductor cross-section	20x
Outer sheath, material	PVC

VIP-PA/20XOE/1,0M/FB3000 - Front adapter



1360225

<https://www.phoenixcontact.com/us/products/1360225>

External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Halogen-free	no

Environmental and real-life conditions

Ambient conditions

Degree of protection (IP20)	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m (above sea level)
Permissible humidity (operation)	≤ 0 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	≤ 95 % (non-condensing)

Approvals

ATEX

Identification	Ⓜ II 3G Ex ec IIC T6 Gc
Certificate	UL 22ATEX2930X

UKEX

Identification	Ⓜ II 3G Ex ec IIC T6 Gc
Certificate	UL 22UKEX2748X

UL, USA/Canada

Identification	Class I, Div. 2, Groups A, B, C, D T6
	Class I, Zone 2, IIC T6

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

VIP-PA/20XOE/1,0M/FB3000 - Front adapter



1360225

<https://www.phoenixcontact.com/us/products/1360225>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1360225>



cUL Recognized

Approval ID: CoC E196811-20230227



UL Recognized

Approval ID: UL CoC



ATEX

Approval ID: UL22ATEX2930X



UKCA-EX

Approval ID: UL22UKEX2748X

VIP-PA/20XOE/1,0M/FB3000 - Front adapter



1360225

<https://www.phoenixcontact.com/us/products/1360225>

Classifications

ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

ETIM

ETIM 10.0	EC002584
-----------	----------

VIP-PA/20XOE/1,0M/FB3000 - Front adapter



1360225

<https://www.phoenixcontact.com/us/products/1360225>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com