

# FOC-TRX-SFP+-10G-LR-IT - Transceiver



1334219

<https://www.phoenixcontact.com/us/products/1334219>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Singlemode SFP+ transceiver for transmission up to 10 Gbps over 10 km at wavelengths of 1,310 nm in the industrial temperature range

## Your advantages

- Maximum flexibility, thanks to the non-proprietary multi-source agreement (MSA)
- Superior system availability, thanks to Plug and Play during operation
- Future-proof, thanks to RoHS 2 conformity
- Maximum data transmission quality
- Interference-free data transmission, even for EMC-sensitive applications
- Reliable data transmission in the extended temperature range

## Commercial data

Item number	1334219
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNJAC
GTIN	4063151631598
Weight per piece (including packing)	34.8 g
Weight per piece (excluding packing)	34.8 g
Customs tariff number	85176200
Country of origin	TW

1334219

<https://www.phoenixcontact.com/us/products/1334219>

## Technical data

### Dimensions

Width	13.7 mm
Height	13 mm
Length	57.3 mm

### Material specifications

Housing material	Metal
------------------	-------

### Interfaces

Transmission speed	10 Gbps
Wavelength	1310 nm

### Product properties

Product type	SFP module
Type	SFP Modul
Connection profile	LC-Duplex
Type of packaging	Box packaging

### Electrical properties

Transmission speed	10 Gbps
Transmission speed	10 Gbps

### Connection data

Connection method	To insert in SFP slot
-------------------	-----------------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

### Standards and regulations

Laser class	1
-------------	---

# FOC-TRX-SFP+-10G-LR-IT - Transceiver



1334219

<https://www.phoenixcontact.com/us/products/1334219>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1334219>



**cULus Recognized**

Approval ID: E140403

# FOC-TRX-SFP+-10G-LR-IT - Transceiver



1334219

<https://www.phoenixcontact.com/us/products/1334219>

## Classifications

### ECLASS

ECLASS-15.0	27440392
ECLASS-13.0	27440392

### ETIM

ETIM 10.0	EC002943
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1334219

<https://www.phoenixcontact.com/us/products/1334219>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	8.121 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)