

# SPE-T1-M12MSM-180 - SPE PCB connector



1363336

<https://www.phoenixcontact.com/us/products/1363336>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SPE PCB connector, design: SPE, degree of protection: IP65/IP67, number of positions: 2, material: LCP, connection method: THR solder connection, cable outlet: straight, color: black, Single Pair Ethernet

## Your advantages

- Connectors in accordance with IEC 63171-5
- THR solderable
- Data transmission up to 600 MHz

## Commercial data

Item number	1363336
Packing unit	80 pc
Minimum order quantity	80 pc
Sales key	AB13
Product key	ABNBEA
GTIN	4063151708221
Weight per piece (including packing)	7.3 g
Weight per piece (excluding packing)	2.553 g
Customs tariff number	85366930
Country of origin	DE

# SPE-T1-M12MSM-180 - SPE PCB connector



1363336

<https://www.phoenixcontact.com/us/products/1363336>

## Technical data

### Product properties

Product type	Data connector (device side)
Type	SPE
Sensor type	Single Pair Ethernet
Number of positions	2
Type of packaging	Tape and Reel
[W] tape width	44.00 mm
[A] coil diameter	330.00 mm
[W2] coil overall dimension	50.40 mm
Number of slots	1
Cable outlet	straight
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	2

### Electrical properties

Maximum load current	4 A
Rated voltage (III/2)	72 V DC
Rated surge voltage	2250 V DC
Rated surge voltage (III/2)	1500 V
Rated current	4 A
Frequency range	600 MHz
Insulation resistance	min. 1 TΩ
Contact resistance	20 mΩ
Transmission medium	Copper
Transmission characteristics (category)	CAT B (IEC 63171)
Transmission speed	1 Gbps
Power transmission	PoDL in accordance with IEEE standard 802.3bt

### Output data

Transmission frequency	600.00 MHz
------------------------	------------

### Connection data

#### Connection technology

Connection method	THR solder connection
-------------------	-----------------------

### Interfaces

Transmission speed	1 Gbps1 Gbps
--------------------	--------------

### Dimensions

# SPE-T1-M12MSM-180 - SPE PCB connector



1363336

<https://www.phoenixcontact.com/us/products/1363336>

Width	12.4 mm
Height	23.8 mm
Length	13.7 mm
Installed height	21.60 mm
Orientation to PCB	180.00 °

## Material specifications

Color	black
Color of the housing part	black
Material Metal surface contact area (top layer)	Au
Material Metal surface contact area (middle layer)	Ni
Material Metal surface soldering area (top layer)	Au
Material Metal surface soldering area (middle layer)	Ni
Flammability rating according to UL 94	V0
Housing material	LCP
Housing surface material	LCP
Contact material	Cu alloy
Contact surface material	Au/Ni

## Cable/line

Test voltage Core/Core	1000 V DC
Test voltage Core/Shield	2250.00 V DC
Test voltage, cable	300 V

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
Insertion force per signal contact	< 30.00 N (in accordance with IEC 63171)
Extraction force per signal contact	< 30 N (in accordance with IEC 63171)
Smallest bending radius	21,2 mm

## Environmental and real-life conditions

### Test specification

Type of test	Vibration test
Specification	IEC 60068-2-6
Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s <sup>2</sup>
Test duration	2.00 h

### Test specification

Specification	IEC 63171
Corrosive stress	IEC 60512-11-7

# SPE-T1-M12MSM-180 - SPE PCB connector



1363336

<https://www.phoenixcontact.com/us/products/1363336>

Contact resistance $R_1$	20.00 m $\Omega$
--------------------------	------------------

## Test specification

Type of test	Mechanical service life with corrosion test
Specification	DIN EN 60512-9-1

## Test specification

Type of test	Shock testing
Specification	IEC 60068-2-27
Acceleration	150.00 m/s <sup>2</sup>
Number of shocks per direction	2000.00

## Mounting


Mounting type	PCB mounting
---------------	--------------

## Processing notes

Process	Reflow
Moisture Sensitive Level	MSL 1
Classification temperature $T_c$	260 °C
Solder cycles in the reflow	3

Drawings

Diagram



Classification reflow soldering profile

# SPE-T1-M12MSM-180 - SPE PCB connector



1363336

<https://www.phoenixcontact.com/us/products/1363336>

## Classifications

### ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

### ETIM

ETIM 10.0	EC002637
-----------	----------

# SPE-T1-M12MSM-180 - SPE PCB connector



1363336

<https://www.phoenixcontact.com/us/products/1363336>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)