

# EMLP (45X15)R BU - Label

1367356

<https://www.phoenixcontact.com/us/products/1367356>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 500, text field height: 15 mm, text field width: 45 mm

## Your advantages

- The EMLP ... self-adhesive markers are particularly suited to marking electrical components, devices, and buttons
- The markers meet the same standards as the engraved labels, they provide high-quality visuals
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Labeling service: Phoenix Contact can custom-label all EMLP ... markers in accordance with your requirements

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1367356       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG16          |
| Product key                          | BG2411        |
| GTIN                                 | 4063151721558 |
| Weight per piece (including packing) | 344.8 g       |
| Weight per piece (excluding packing) | 344.8 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

### Marking

|                                     |                |
|-------------------------------------|----------------|
| Number of individual labels         | 500            |
| Number of individual labels per row | 1              |
| Identification technology           | Thermotransfer |

### Dimensions

|        |          |
|--------|----------|
| Width  | 45.00 mm |
| Height | 15.00 mm |
| Depth  | 0.55 mm  |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 45 mm |
| Text field height | 15 mm |

### Material specifications

|                       |                 |
|-----------------------|-----------------|
| Color                 | blue (RAL 5015) |
| Base element material | Polyester       |
| Components            | Silicone-free   |

### Environmental and real-life conditions

#### Ambient conditions

|   |                   |
|---|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 120 °C |
| Recommended ambient temperature (storage/transport) | 20 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

#### Test for substances that would hinder coating with paint or varnish

|   |                      |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result  | Test passed          |

#### Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

#### Tesafilm test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

# EMLP (45X15)R BU - Label



1367356

<https://www.phoenixcontact.com/us/products/1367356>

|               |                         |
|---------------|-------------------------|
| Result        | Test passed             |
| Test duration | 96 h                    |
| Procedure     | Artificial irradiation. |

## Temperature storage

|                         |                       |
|-------------------------|-----------------------|
| Specification           | IEC 60068-2-2:2007-07 |
| Result                  | Test passed           |
| Procedure               | Test Bb               |
| Duration                | 96 h                  |
| Temperature for testing | 120 °C                |

## Wipe resistance of inscriptions

|   |  |
|---|--|
| Specification                                   | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                     | Test passed  |
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed  |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed  |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                          |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result        | Test passed              |
| Procedure     | Method B                 |
| Cycles        | 2                        |

## Salt spray test

|               |   |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h  |

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# EMLP (45X15)R BU - Label

1367356

<https://www.phoenixcontact.com/us/products/1367356>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# EMLP (45X15)R BU - Label



1367356

<https://www.phoenixcontact.com/us/products/1367356>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)