

# PT 2,5-PE/L/L/L - Multi-level terminal block



1336407

<https://www.phoenixcontact.com/us/products/1336407>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multi-level terminal block, number of connections: 8, number of positions: 4, connection method: Push-in connection, Protective conductor connection, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 4 mm<sup>2</sup>, connection method: Push-in connection, Feed-through level, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: gray

## Your advantages

- Time-saving conductor connection thanks to tool-free direct-connection technology
- Vibration-resistant and maintenance-free conductor connection
- Full flexibility thanks to the standardized CLIPLINE complete bridging, marking, and testing accessories
- Meet the requirements of DIN EN 60947-7-2 or IEC 60947-7-2 for protective conductor connections
- High level of safety thanks to the low-resistance connection to the ground potential via the top-hat rail
- Direct contacting with the DIN rail enables fast, error-free grounding without additional wiring effort.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1336407       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE22          |
| Product key                          | BE2216        |
| GTIN                                 | 4063151637231 |
| Weight per piece (including packing) | 31.58 g       |
| Weight per piece (excluding packing) | 22.22 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# PT 2,5-PE/L/L/L - Multi-level terminal block



1336407

<https://www.phoenixcontact.com/us/products/1336407>

## Technical data

### Notes

#### General

|      |   |
|------|---|
| Note | When establishing a connection on the open housing side of a feed-through modular terminal block of the same series and size, the block must be provided with a cover if the expected insulation voltage is >690 V. |
|      | The max. load current must not be exceeded by the total current of all connected conductors.  |

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | Ground terminal block |
| Product family        | PT                    |
| Number of positions   | 4                     |
| Number of connections | 8                     |
| Number of rows        | 4                     |

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                     |      |
|---------------------|------|
| Rated surge voltage | 6 kV |
|---------------------|------|

### Connection data

|                                 |                     |
|---------------------------------|---------------------|
| Number of connections per level | 2                   |
| Nominal cross section           | 2.5 mm <sup>2</sup> |

#### Protective conductor connection

|   |  |
|---|--|
| Connection method   | Push-in connection                           |
| Stripping length  | 8 mm ... 10 mm                               |
| Internal cylindrical gage   | A3<br>B3                                     |
| Connection in acc. with standard                                  | IEC 60947-7-2                                |
| Conductor cross-section rigid                                     | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Cross section AWG   | 26 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible                                  | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG]                           | 26 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible ultrasound-compressed            | 0.34 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG] ultrasound-compressed     | 22 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Nominal cross section   | 2.5 mm <sup>2</sup>                          |

#### Feed-through level

# PT 2,5-PE/L/L/L - Multi-level terminal block



1336407

<https://www.phoenixcontact.com/us/products/1336407>

|   |   |
|---|---|
| Connection method   | Push-in connection                                    |
| Stripping length  | 8 mm ... 10 mm  |
| Connection in acc. with standard                                  | IEC 60947-7-1   |
| Conductor cross-section rigid                                     | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| Cross section AWG   | 26 ... 12 (converted acc. to IEC)                     |
| Conductor cross-section flexible                                  | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| Conductor cross-section, flexible [AWG]                           | 26 ... 12 (converted acc. to IEC)                     |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>          |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>          |
| Nominal cross section   | 2.5 mm <sup>2</sup>                                   |
| Nominal current   | 18 A  |
| Maximum load current  | 20 A (with 4 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage   | 500 V   |

## Protective conductor connection Connection cross sections directly pluggable

|   |   |
|---|---|
| Conductor cross-section rigid                                     | 0.34 mm <sup>2</sup> ... 4 mm <sup>2</sup>  |
| Conductor cross-section, rigid [AWG]                              | 20 ... 12 (converted acc. to IEC)           |
| Conductor cross-section flexible                                  | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |

## Feed-through level Connection cross sections directly pluggable

|   |   |
|---|---|
| Conductor cross-section rigid                                     | 0.34 mm <sup>2</sup> ... 4 mm <sup>2</sup>  |
| Conductor cross-section, rigid [AWG]                              | 20 ... 12 (converted acc. to IEC)           |
| Conductor cross-section flexible                                  | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |

## Dimensions

|                    |          |
|--------------------|----------|
| Width              | 5.2 mm   |
| End cover width    | 2.2 mm   |
| Height             | 142.4 mm |
| Depth on NS 35/7,5 | 68.6 mm  |
| Depth on NS 35/15  | 76.1 mm  |

## Material specifications

|  |                 |
|--|-----------------|
| Color  | gray (RAL 7042) |
| Flammability rating according to UL 94                           | V0              |
| Insulating material group  | I               |
| Insulating material  | PA              |
| Static insulating material application in cold                   | -60 °C          |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3     |

# PT 2,5-PE/L/L/L - Multi-level terminal block



1336407

<https://www.phoenixcontact.com/us/products/1336407>

|   |             |
|---|-------------|
| Fire protection for rail vehicles (DIN EN 45545-2) R26  | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162)              | passed      |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed      |
| Smoke gas toxicity NFPA 130 (SMP 800C)                  | passed      |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Oscillation/broadband noise

|                        |  |
|------------------------|--|
| Specification          | DIN EN 50155 (VDE 0115-200):2022-06              |
| Spectrum               | Long life test category 1, class B, body mounted |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$   |
| ASD level              | $0.964 \text{ (m/s}^2\text{)}/\text{Hz}$         |
| Acceleration           | 0.58g  |
| Test duration per axis | 5 h  |
| Test directions        | X-, Y- and Z-axis                                |
| Result                 | Test passed                                      |

### Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2022-06 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 5g                                  |
| Shock duration                 | 30 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-2 |
|                                  | IEC 60947-7-1 |

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|---------------|-----------|

# PT 2,5-PE/L/L/L - Multi-level terminal block



1336407


<https://www.phoenixcontact.com/us/products/1336407>

---

NS 35/15

Drawings

Circuit diagram



# PT 2,5-PE/L/L/L - Multi-level terminal block



1336407

<https://www.phoenixcontact.com/us/products/1336407>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1336407>

 **CSA**  
Approval ID: 13631

 **cULus Recognized**  
Approval ID: E60425

|               | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---------------|-----------------------|-----------------------|-------------------|-----------------------------|
| <b>B</b>      |                       |                       |                   |                             |
|               | 300 V                 | 18 A                  | 26 - 12           | -                           |
| PE connection | -                     | -                     | 26 - 12           | -                           |
| <b>C</b>      |                       |                       |                   |                             |
|               | 300 V                 | 18 A                  | 26 - 12           | -                           |
| PE connection | -                     | -                     | 26 - 12           | -                           |
| <b>F</b>      |                       |                       |                   |                             |
|               | 500 V                 | 18 A                  | 26 - 12           | -                           |
| <b>D</b>      |                       |                       |                   |                             |
|               | 600 V                 | 5 A                   | 26 - 12           | -                           |
| PE connection | -                     | -                     | 26 - 12           | -                           |

# PT 2,5-PE/L/L/L - Multi-level terminal block



1336407

<https://www.phoenixcontact.com/us/products/1336407>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250104 |
| ECLASS-15.0 | 27250104 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000901 |
|-----------|----------|

# PT 2,5-PE/L/L/L - Multi-level terminal block



1336407

<https://www.phoenixcontact.com/us/products/1336407>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)