


# CUC-COX-J1M-A/LBS - Coaxial PCB connector



1340152

<https://www.phoenixcontact.com/us/products/1340152>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coaxial PCB connector, degree of protection: IP20, number of positions: 1, 12 Gbps, material: Metal, connection method: Solder connection, cable outlet: straight

## Your advantages

- Future-proof, thanks to the use of lead-free materials
- Complete documentation saves developers time during design-in
- Ideal for WLAN, Bluetooth, LTE, and 5G signals

## Commercial data

Item number	1340152
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AB14
Product key	ABNFBB
GTIN	4063151646066
Weight per piece (including packing)	6.43 g
Weight per piece (excluding packing)	6.43 g
Customs tariff number	85366910
Country of origin	DE

1340152

<https://www.phoenixcontact.com/us/products/1340152>

## Technical data

### Product properties

Product type	Data connector (device side)
Type	Coaxial
Number of positions	1
Connection profile	R-SMA (f)
Type of packaging	PE bag
Cable outlet	straight
Thread type	1/4-36 UNS

### Electrical properties

Rated surge voltage (III/2)	1500 V
Frequency range	10 Hz
Test voltage	1000 V <sub>rms</sub>
Transmission medium	Copper
Transmission speed	12.4 Gbps

### Output data

Transmission frequency	1.00 GHz
------------------------	----------

### Connection data

#### Connection technology

Connection method	Solder connection
Locking mechanism tightening torque	1.10 Nm

### Dimensions

Width	7 mm
Height	14 mm
Length	19.5 mm
Installed height	10.00 mm
Orientation to PCB	90.00 °

### Material specifications

Material	Metal
Flammability rating according to UL 94	V0
Housing material	Metal
Contact material	CuBe2
Contact surface material	NiP-Au

### Cable/line

Halogen-free	no
--------------	----

### Mechanical properties

# CUC-COX-J1M-A/LBS - Coaxial PCB connector



1340152

<https://www.phoenixcontact.com/us/products/1340152>

## Mechanical data

Insertion/withdrawal cycles	> 100
Extraction force per signal contact	< 20 N
Locking mechanism tightening torque	1.10 Nm

## Environmental and real-life conditions

### Test specification

Specification	DIN EN 61169-1
Contact resistance $R_2$	2.00 m $\Omega$
Insulation resistance, neighboring contacts	5 G $\Omega$
Impulse withstand voltage at sea level	1400.00 V DC
Power-frequency withstand voltage	1000.00 V AC

### Test specification

Specification	DIN EN 60068-2-14 Test Na
Cold stress	-10°C

### Test specification

Specification	DIN EN 60068-2-6 Test Fc
Frequency	10-2000-10 Hz
Sweep speed	1 octave/min
Amplitude	0.75 mm
Acceleration	100.00 m/s <sup>2</sup>
Test duration	2.50 h

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 125 °C
Ambient temperature (storage/transport)	-55 °C ... 125 °C


## Mounting

Mounting type	Wave soldering
---------------	----------------

### Processing notes

Process	THR
Moisture Sensitive Level	MSL 1

Drawings



Classification wave soldering profile

# CUC-COX-J1M-A/LBS - Coaxial PCB connector



1340152

<https://www.phoenixcontact.com/us/products/1340152>

## Classifications

### ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

### ETIM

ETIM 10.0	EC002637
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CUC-COX-J1M-A/LBS - Coaxial PCB connector



1340152

<https://www.phoenixcontact.com/us/products/1340152>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	1.383 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)