

# TRIO-BAT/PB/24DC/4AH - Battery module



1394730

<https://www.phoenixcontact.com/us/products/1394730>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Battery module (device with battery), VRLA-AGM, 24 V DC, 4 Ah

## Product description

The perfect addition to the TRIO UPS modules. Battery modules with lead AGM technology are fully charged before being sent to our warehouse.

## Your advantages

- Long buffer times under normal conditions
- Convenient panel mounting or DIN rail mounting
- Comprehensive approval package, compatible with TRIO UPS
- TRIO UPS modules have a uniform design
- Easy handling with preassembled cables and fuse holders
- Immediate availability: All energy storage systems leave our warehouse fully charged

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1394730       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CM24          |
| Product key                          | CMUEV3        |
| GTIN                                 | 4063151776831 |
| Weight per piece (including packing) | 4,259 g       |
| Weight per piece (excluding packing) | 3,778 g       |
| Customs tariff number                | 85072080      |
| Country of origin                    | CN            |

# TRIO-BAT/PB/24DC/4AH - Battery module



1394730

<https://www.phoenixcontact.com/us/products/1394730>

## Technical data

### Notes

#### General

|                     |                                                                                                                                                                                                                                                                                   |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on the battery | This product contains a battery with a limited shelf life that must be charged every few months. The product packaging indicates when the battery must be started up or recharged. The general shelf life can be found in the energy storage devices area under "Latest startup". |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Energy storage

#### Input

|                       |                |
|-----------------------|----------------|
| Input voltage         | 24 V DC (SELV) |
| Nominal capacity      | 4 Ah           |
| Charging current      | max. 1.2 A     |
| End-of-charge voltage | 27.6 V (20 °C) |

#### Output

|                          |                                             |
|--------------------------|---------------------------------------------|
| Output current           | max. 25 A                                   |
| Output fuse              | 1x 25 A T 25A 32V, ATOF 287 from Littelfuse |
| Buffer time              | 4.5 min (20 A)                              |
|                          | 3 min (25 A)                                |
| End-of-discharge voltage | 19.2 V                                      |

#### General

|                                    |                             |
|------------------------------------|-----------------------------|
| Connection in parallel             | yes                         |
| Battery type                       | BB Battery HR4.2-12FR       |
| Battery technology                 | VRLA-AGM                    |
| IQ-Technology                      | no                          |
| Latest startup date (battery only) | 9 Months (-20 °C ... 20 °C) |
|                                    | 6 Months (25 °C)            |
|                                    | 3 Months (30 °C)            |
| Service life                       | 6 Years (20 °C)             |
| Size designation                   | Block                       |
| Temperature sensor                 | no                          |

### Product properties

|                |                                                                                                                                                     |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|
| Product type   | Battery module                                                                                                                                      |
| Product family | Battery module (device with battery)                                                                                                                |
| Application    | TRIO-UPS-2G                                                                                                                                         |
| Disposal       | Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations. |

#### Insulation characteristics

# TRIO-BAT/PB/24DC/4AH - Battery module



1394730

<https://www.phoenixcontact.com/us/products/1394730>

|                     |     |
|---------------------|-----|
| Protection class    | III |
| Degree of pollution | 2   |

## Dimensions

### Item dimensions

|        |        |
|--------|--------|
| Width  | 115 mm |
| Height | 154 mm |
| Depth  | 113 mm |

### Drill hole

|          |      |
|----------|------|
| Diameter | 5 mm |
|----------|------|

### Installation dimensions

|                                  |             |
|----------------------------------|-------------|
| Installation distance right/left | 0 mm / 0 mm |
| Installation distance top/bottom | 5 mm / 5 mm |

## Mounting

|                   |                                     |
|-------------------|-------------------------------------|
| Mounting type     | DIN rail mounting                   |
| Mounting position | horizontal DIN rail NS 35, EN 60715 |

## Material specifications

|                  |       |
|------------------|-------|
| Housing material | Metal |
|------------------|-------|

## Cable/line

### Battery connecting cable:

|                     |                   |
|---------------------|-------------------|
| Cable cross section | 4 mm <sup>2</sup> |
| Cable length        | 2000 mm           |
| Color               | red               |

### Battery connecting cable:

|                     |                   |
|---------------------|-------------------|
| Cable cross section | 4 mm <sup>2</sup> |
| Cable length        | 2000 mm           |
| Color               | black             |

## Environmental and real-life conditions

### Ambient conditions

|                                                |                  |
|------------------------------------------------|------------------|
| Degree of protection                           | IP20             |
| Ambient temperature (storage/transport)        | -20 °C ... 40 °C |
| Ambient temperature (charge)                   | 0 °C ... 40 °C   |
| Ambient temperature (discharge)                | -20 °C ... 50 °C |
| Max. permissible relative humidity (operation) | ≤ 95 %           |

## Ex data

|                            |    |
|----------------------------|----|
| Suited for EX-applications | no |
|----------------------------|----|


TRIO-BAT/PB/24DC/4AH - Battery module



1394730  
<https://www.phoenixcontact.com/us/products/1394730>


Drawings

Graphic



TRIO battery buffer times for TRIO UPS 2G

Graphic



TRIO battery buffer times for TRIO3 UPS

# TRIO-BAT/PB/24DC/4AH - Battery module



1394730

<https://www.phoenixcontact.com/us/products/1394730>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1394730>



**IECEE CB Scheme**  
Approval ID: DK-139600-UL



**cULus Listed**  
Approval ID: E123528

**DNV**

Approval ID: TAA00002EW



**cULus Listed**  
Approval ID: E199827-20230421

# TRIO-BAT/PB/24DC/4AH - Battery module



1394730

<https://www.phoenixcontact.com/us/products/1394730>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27050403 |
| ECLASS-15.0 | 27050403 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003893 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26111700 |
|-------------|----------|

# TRIO-BAT/PB/24DC/4AH - Battery module



1394730

<https://www.phoenixcontact.com/us/products/1394730>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-8                                                                                                                                                                                                                            |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                      |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)