

# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable



1396040

<https://www.phoenixcontact.com/us/products/1396040>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, shielded, Socket straight M8, coding: A, on Socket straight M8, cable length: 5 m

## Commercial data

Item number	1396040
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1BJA
GTIN	4063151780500
Weight per piece (including packing)	182 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable



1396040

<https://www.phoenixcontact.com/us/products/1396040>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	4
No. of cable outlets	1
Shielded	yes
Coding	A

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	4 A

### Signaling

Status display	no
Status display present	no

### Connector

#### Connection 1

Type	Socket straight M8
Number of positions	4
Coding type	A

#### Connection 2

Type	Socket straight M8
Number of positions	4

### Cable/line

Cable length	5 m
--------------	-----

# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable

1396040

<https://www.phoenixcontact.com/us/products/1396040>

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	31 kg/km
UL AWM Style	20549
Number of positions	4
Shielded	yes
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	4x 0.25 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.02 mm (Signal line)
External cable diameter	4.70 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation) approx. 0.50 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Optical shield covering	80 %
Max. conductor resistance	max. 78 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	24 mm
Smallest bending radius, movable installation	48 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 48 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥2000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1 Highly resistant to acids, alkaline solutions and solvents

# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable



1396040

<https://www.phoenixcontact.com/us/products/1396040>

Other resistance	hydrolysis and microbe resistant
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable

1396040

<https://www.phoenixcontact.com/us/products/1396040>

## Drawings

Dimensional drawing



Socket M8 x 1, straight, shielded

Dimensional drawing




Socket M8 x 1, straight, shielded

# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable

1396040

<https://www.phoenixcontact.com/us/products/1396040>

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side


# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable



1396040

<https://www.phoenixcontact.com/us/products/1396040>

Circuit diagram



Contact assignment of M8 socket

# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable



1396040

<https://www.phoenixcontact.com/us/products/1396040>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1396040>

 <b>UL Listed</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	4 A	-	-

 <b>cUL Listed</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	4 A	-	-

# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable



1396040

<https://www.phoenixcontact.com/us/products/1396040>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-4P-M 8FS/ 5,0-PUR/M 8FSSH - Sensor/actuator cable



1396040

<https://www.phoenixcontact.com/us/products/1396040>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)