

1343386

<https://www.phoenixcontact.com/us/products/1343386>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail distributor 6x LC duplex

Distributor, design: Rail-mountable module, degree of protection: IP20, material: Metal, connection method: Splicing, cable outlet: above and below, housing size: 1, color: gray

## Product description

FDX 20 series DIN rail distributor box without pigtails, assembled with 6x LC duplex coupling, singlemode. Splice holder for separately available shrink and crimp splicing protection, on a patented splice comb made from powder-coated sheet steel. Cable insertion possible via cable gland from above or below.

Housing, 2-part, prepared for DIN rail mounting through the rear-side adapter. The adapter can also be mounted on the side.

Scope of supply:

DIN rail housing with integrated splice comb (mounted), assembled with 6x LC duplex coupling, 1x splice holder, 1x cable gland (M20x1.5)

## Your advantages

- Intuitive front-panel operation and clear control cabinet layout thanks to uniform design
- Flexible DIN rail mounting possible in six positioning directions
- Suitable for industrial applications
- Continuously reliable data connection, thanks to extensively tested components
- Snap-on mounting on standard DIN rails NS 35/7.5 or NS 35/15
- Perfectly sized and patented pigtail tray for convenient splicing and compact bending radii.
- For easy field connection

## Commercial data

Item number	1343386
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB15
Product key	ABNGAB
GTIN	4063151654955
Weight per piece (including packing)	655.8 g
Weight per piece (excluding packing)	573.74 g
Customs tariff number	85367000
Country of origin	DE

1343386

<https://www.phoenixcontact.com/us/products/1343386>

## Technical data

### Notes

Order information:	Wire pigtails must be ordered separately
--------------------	------------------------------------------

### Product properties

Product type	Network distributor box
Series	FDX 20 series
Type	Rail-mountable module
No. of cable outlets	2
Number of module slots	6
Number of slots	12
Type of the screw connection	M20 x 1.5
Protective cover	yes
Cable outlet	above and below

### Electrical properties

Transmission medium	FO
---------------------	----

### Connection data

#### Connection technology

Connection method	Splicing
-------------------	----------

### Dimensions

Width	40 mm
Height	130 mm
Depth	115 mm

#### Housing

Housing width	40 mm
---------------	-------

#### Mechanical characteristics

Ferrule diameter	1.25 mm
------------------	---------

### Material specifications

Color	gray
Flammability rating according to UL 94	V0
Ferrule material	Zirconia ceramics
Housing material	Metal
Housing surface material	Powder-coated, gray

### Cable/line

Cable type	Fiberglass
External cable diameter	6 mm ... 12 mm

1343386

<https://www.phoenixcontact.com/us/products/1343386>

External cable diameter	6 mm ... 12 mm
Resistance to oil	no
Flame resistance	yes

## FO cable

Fiber	GOF
Fiber type	Single-mode fiberglass
Transmission medium	FO

## Mechanical properties

### Mechanical data

Type of the screw connection	M20 x 1.5
Insertion/withdrawal cycles	≥ 500

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20 (according to IEC 60529)
	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (Category OPhd+)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	0 °C ... 55 °C
Resistance to oil	no

## Standards and regulations

Flame resistance	yes
Resistance to oil	no

## Mounting

Mounting type	DIN rail mounting
Assembly note	Option for flexible replugging of DIN rail adapter

1343386

<https://www.phoenixcontact.com/us/products/1343386>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1343386>



**UL Listed**

Approval ID: E335024-20250729



**cUL Listed**

Approval ID: E335024-20250729

1343386

<https://www.phoenixcontact.com/us/products/1343386>

## Classifications

### ECLASS

ECLASS-13.0	19170113
ECLASS-15.0	19170113

### ETIM

ETIM 10.0	EC002699
-----------	----------

### UNSPSC

UNSPSC 21.0	43223300
-------------	----------

1343386

<https://www.phoenixcontact.com/us/products/1343386>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)