

FL MGUARD 2105 - Router

1357850

<https://www.phoenixcontact.com/us/products/1357850>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the standard item

Security-Router series, 5 RJ45 ports 10/100/1000 Mbps, degree of protection: IP20, Ambient temperature (operation): -20 °C ... 60 °C, Supply voltage range: 12 V DC ... 36 V DC, NAT, VPN, unmanaged, 4-port switch, development process certified in accordance with IEC 62443-4-1, Product certified in accordance with IEC 62443-4-2, Simple stateful inspection firewall, safe isolation for PROFI-safe in accordance with IEC 61784-3-3

Product description

Security remote maintenance router

Your advantages

- Central management tool
- Maximum performance
- Maximum security
- Remote maintenance with maximum security
- mGuard security technology

Commercial data

Item number	1357850
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN28
Product key	DNN311
GTIN	4063151686819
Weight per piece (including packing)	400 g
Weight per piece (excluding packing)	327 g
Customs tariff number	85176200
Country of origin	DE

FL MGUARD 2105 - Router



1357850

<https://www.phoenixcontact.com/us/products/1357850>

Technical data

Dimensions

Width	45 mm
Height	130 mm
Depth	133.8 mm

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Material specifications

Color (Housing)	light gray (RAL 7035)
Housing material	Plastic

Interfaces

Ethernet

Connection method	RJ45
Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
No. of channels	5 (RJ45 ports)

2x digital output, 2x digital input

Connection method	Push-in-/Spring-cage connection
Additional text	not electrically isolated

VPN - release button

Connection method	Push-in-/Spring-cage connection
-------------------	---------------------------------

System properties

Functionality

Basic functions	Router with firewall and VPN for 2 tunnels (fixed), plastic housing, slot for SD memory card, extended temperature range, router with firewall and VPN for 2 tunnels (fixed), plastic housing, slot for SD memory card, extended temperature range, integrated 4-port switch
-----------------	--

System requirements

Supported browsers	HTTPS support required
--------------------	------------------------

Product properties

Product type	Security router for the DIN rail
Product family	Security-Router

Type	Stand-alone
Special properties	NAT
	VPN
	unmanaged, 4-port switch, development process certified in accordance with IEC 62443-4-1
	Product certified in accordance with IEC 62443-4-2

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Security functions

1:1 Network Address Translation (NAT) in the VPN	supported
Number of VPN tunnels	2 (Fixed, Ipsec (IETF standard))
Authentication	X.509v3 certificates with RSA or PSK
Data integrity	MD5, SHA-1, SHA 256, SHA-512
Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Filtering	Incoming or outgoing traffic
Firewall data throughput	max. 940 Mbps (Router mode, default firewall rules, unidirectional throughput)
	max. 850 Mbps (Stealth mode, default firewall rules, unidirectional throughput)
Firewall rules	Simple stateful inspection firewall, safe isolation for PROFIsafe in accordance with IEC 61784-3-3
Basic functions	Router with firewall and VPN for 2 tunnels (fixed), plastic housing, slot for SD memory card, extended temperature range, router with firewall and VPN for 2 tunnels (fixed), plastic housing, slot for SD memory card, extended temperature range, integrated 4-port switch
Internet Protocol Security (IPsec) mode	ESP tunnel / ESP transport
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Network Time Protocol (NTP) client	Client/server
Remote Syslog Logging	on external server
Routing	Standard routing, NAT, 1:1-NAT, port forwarding
Protection against	IP spoofing, DoS and Syn Flood Protection
Encryption methods	DES, 3DES, AES-128, -192, -256
Virtual private network (VPN) throughput	max. 250 Mbps (Router mode, VPN unidirectional throughput)

Electrical properties

Local diagnostics	US1 Supply voltage US1 Green LED
	One LED per port Link active / Speed Green / green/yellow LED
Maximum power dissipation for nominal condition	typ. 2.88 W

Supply

Supply voltage (DC)	24 V DC
Supply voltage range	12 V DC ... 36 V DC
Power supply connection	via COMBICON, max. conductor cross-section 1.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	1 A

Typical current consumption	120 mA (at $U_S = 24$ V DC)
-----------------------------	-----------------------------

Function

Signal contact control voltage	24 V DC (typical)
Signal contact control current	250 mA (short-circuit-proof)

Connection data

Connection method	RJ45 jack, shielded
Connection method	Push-in spring connection
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Standards and regulations

Free from substances that could impair the application of coating	Yes
---	-----

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) 6 kV contact discharge, 8 kV air discharge
	IEC 61000-6-2 IEC 61000-4-3 (immunity to radiated interference) 10 V/m (80 MHz ... 6000 MHz)
	IEC 61000-6-2 IEC 61000-4-4 (burst) 2 kV power line, 2 kV data line
	IEC 61000-6-2 IEC 61000-4-5 (surge) power line: 1 kV (line/earth), 0.5 kV (line/line), 1 kV data line
	IEC 61000-6-2 IEC 61000-4-6 (immunity to conducted interference) 10 V (150 kHz ... 80 MHz)
Noise immunity	EN 61000-6-2:2005

Noise emission

FL MGUARD 2105 - Router



1357850

<https://www.phoenixcontact.com/us/products/1357850>

Standards/regulations

EN 61000-6-4

Signaling

Status display

LEDs: US1, FAIL, Link, and Activity

FL MGUARD 2105 - Router



1357850

<https://www.phoenixcontact.com/us/products/1357850>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1357850>



cUL Listed

Approval ID: E238705

Cybersecurity Certificate

Approval ID: 968 CSP 1029.00 25



cUL Listed

Approval ID: E238705



cULus Listed

Approval ID: E366272



cULus Listed

Approval ID: E366272

FL MGUARD 2105 - Router

1357850

<https://www.phoenixcontact.com/us/products/1357850>



Classifications

ECLASS

ECLASS-13.0	19170406
ECLASS-15.0	19170406

ETIM

ETIM 10.0	EC001478
-----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

1357850

<https://www.phoenixcontact.com/us/products/1357850>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	4,4'-isopropylidenediphenol(CAS: 80-05-7)
	Lead(CAS: 7439-92-1)

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com