


FOC-LC:A-LC:A-GZ02/2 - FO patch cable



1400621

<https://www.phoenixcontact.com/us/products/1400621>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled FO cable, zip cord cable, multi-mode fiberglass 50/125 μm , OM3, plug: LC/LC, degree of protection: IP20, for installation in cable ducts or control cabinets, length: 2 m

Your advantages

- Multi-mode patch cable for indoor installation
- Ideal for use in distributor systems and for connecting termination devices
- All components satisfy UL 94, V0
- 2.8 mm single elements made from halogen-free and flame-retardant material
- Interferometer tests at every stage of the certification process
- Excellent mechanical and optical properties
- Satisfies optical and mechanical industry standards
- Connector with UPC polishing for optimum attenuation values
- Insertion loss ≤ 0.5 dB
- Return attenuation ≥ 35 dB

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1400621 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB16 |
| Product key | ABNIBC |
| GTIN | 4046356734769 |
| Weight per piece (including packing) | 43.2 g |
| Weight per piece (excluding packing) | 40.5 g |
| Customs tariff number | 85447000 |
| Country of origin | DE |

1400621

<https://www.phoenixcontact.com/us/products/1400621>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Number of positions | 2 |
| No. of conductors | 2 |

Electrical properties

| | |
|---------------------|-------------------------|
| Attenuation | ≤ 0.5 dB (with 850 nm) |
| | ≤ 0.5 dB (with 1300 nm) |
| Transmission medium | Multi-mode fiberglass |

Mechanical properties

| | |
|---------------------------------------|------|
| Tensile strength short-term/long-term | 50 N |
|---------------------------------------|------|

Mechanical data

| | |
|-------------------------|-------|
| Smallest bending radius | 30 mm |
|-------------------------|-------|

Material specifications

| | |
|--|-------------------|
| Color | blue |
| Flammability rating according to UL 94 | V0 |
| Ferrule material | Zirconia ceramics |

Dimensions

External dimensions

| | |
|------------------------|--------|
| External diameter min. | 2.8 mm |
| External diameter max. | 5.7 mm |

Mechanical characteristics

| | |
|------------------|---------|
| Ferrule diameter | 1.25 mm |
|------------------|---------|

Connector

Connection 1

| | |
|----------------------|------------------|
| Type | Plug straight LC |
| Degree of protection | IP20 |

Connection 2

| | |
|------|------------------|
| Type | Plug straight LC |
|------|------------------|

Cable/line

| | |
|--------------|------------|
| Cable length | 2.00 m |
| Cable weight | 8.30 kg/km |
| Cable type | Fiberglass |
| Cable type | Zip cord |

FOC-LC:A-LC:A-GZ02/2 - FO patch cable



1400621

<https://www.phoenixcontact.com/us/products/1400621>

| | |
|---|---|
| External cable diameter | 2.00 mm (Zip cord) |
| Outer sheath, material | LSZH |
| External sheath, color | aqua |
| Wire diameter incl. insulation | 900 µm |
| Individual wire diameter | 900 µm (low-bend) |
| Single wire, color | - |
| Tensile strength short-term/long-term | 600 N |
| Smallest bending radius, fixed installation | 15 mm |
| Smallest bending radius, movable installation | 30 mm |
| Cable, attenuation | 2.5 dB/km (at 850 nm), 0.7 dB/km (at 1300 nm) |
| Halogen-free | complying with IEC 60754-1/2 |
| Flame resistance | yes |

FO cable

| | |
|---------------------|---|
| Number of fibers | 2 |
| Fiber | 50/125 µm |
| Fiber type | Multimode fiberglass 50/125 µm |
| Cable, attenuation | 2.5 dB/km (at 850 nm), 0.7 dB/km (at 1300 nm) |
| Transmission medium | Multi-mode fiberglass |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -10 °C ... 60 °C |
| Ambient temperature (storage/transport) | -10 °C ... 60 °C |
| Ambient temperature (assembly) | -5 °C ... 50 °C |
| Ambient temperature (installation) | -5 °C ... 50 °C |

Standards and regulations

| | |
|------------------|-----|
| Flame resistance | yes |
|------------------|-----|

FOC-LC:A-LC:A-GZ02/2 - FO patch cable



1400621

<https://www.phoenixcontact.com/us/products/1400621>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121607 |
|-------------|----------|

FOC-LC:A-LC:A-GZ02/2 - FO patch cable



1400621

<https://www.phoenixcontact.com/us/products/1400621>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com