

SPE-T1-M12FSF-180 - SPE PCB connector



1363337

<https://www.phoenixcontact.com/us/products/1363337>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SPE PCB connector, design: SPE, degree of protection: IP65/IP67, number of positions: 2, material: LCP, connection method: THR solder connection, cable outlet: straight, color: black, Single Pair Ethernet

Your advantages

- Easily integrated: M12 male and female versions for established inductive sensors and flying leads
- Cross-application: range of up to 1000 m, data rates of up to 1 Gbps, and power of up to 50 W
- Totally protected: Advanced Shielding Technology provides a reliable shield connection for network cables, even under extreme environmental conditions
- Future-proof: standardized connectors and cables in accordance with IEC 63171-5

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1363337 |
| Packing unit | 80 pc |
| Minimum order quantity | 80 pc |
| Sales key | AB13 |
| Product key | ABNBEA |
| GTIN | 4063151707859 |
| Weight per piece (including packing) | 6.468 g |
| Weight per piece (excluding packing) | 2.333 g |
| Customs tariff number | 85366930 |
| Country of origin | DE |

SPE-T1-M12FSF-180 - SPE PCB connector



1363337

<https://www.phoenixcontact.com/us/products/1363337>

Technical data

Product properties

| | |
|-----------------------------|------------------------------|
| Product type | Data connector (device side) |
| Type | SPE |
| Sensor type | Single Pair Ethernet |
| Number of positions | 2 |
| Type of packaging | Tape and Reel |
| [W] tape width | 44.00 mm |
| [A] coil diameter | 330.00 mm |
| [W2] coil overall dimension | 38.40 mm |
| Number of slots | 1 |
| Cable outlet | straight |
| Thread type | M12 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 2 |

Electrical properties

| | |
|---|---|
| Maximum load current | 4 A |
| Rated voltage (III/2) | 72 V DC |
| Rated surge voltage | 2250 V DC |
| Rated surge voltage (III/2) | 1500 V |
| Rated current | 4 A |
| Frequency range | 600 MHz |
| Insulation resistance | min. 1 TΩ |
| Contact resistance | 20 mΩ |
| Transmission medium | Copper |
| Transmission characteristics (category) | CAT B (IEC 63171) |
| Transmission speed | 1 Gbps |
| Power transmission | PoDL in accordance with IEEE standard 802.3bt |

Output data

| | |
|------------------------|------------|
| Transmission frequency | 600.00 MHz |
|------------------------|------------|

Connection data

Connection technology

| | |
|-------------------|-----------------------|
| Connection method | THR solder connection |
|-------------------|-----------------------|

Interfaces

| | |
|--------------------|--------------|
| Transmission speed | 1 Gbps1 Gbps |
|--------------------|--------------|

Dimensions

SPE-T1-M12FSF-180 - SPE PCB connector



1363337

<https://www.phoenixcontact.com/us/products/1363337>

| | |
|--------------------|----------|
| Width | 12.4 mm |
| Height | 19.4 mm |
| Length | 13.7 mm |
| Installed height | 21.60 mm |
| Orientation to PCB | 180.00 ° |

Material specifications

| | |
|--|----------|
| Color | black |
| Color of the housing part | black |
| Flammability rating according to UL 94 | V0 |
| Housing material | LCP |
| Housing surface material | LCP |
| Contact material | Cu alloy |
| Contact surface material | Au/Ni |

Cable/line

| | |
|--------------------------|--------------|
| Test voltage Core/Core | 1000 V DC |
| Test voltage Core/Shield | 2250.00 V DC |
| Test voltage, cable | 300 V |

Mechanical properties

Mechanical data

| | |
|-------------------------------------|--|
| Insertion/withdrawal cycles | > 100 |
| Insertion force per signal contact | < 30.00 N (in accordance with IEC 63171) |
| Extraction force per signal contact | < 30 N (in accordance with IEC 63171) |
| Smallest bending radius | 21,2 mm |

Environmental and real-life conditions

Test specification

| | |
|---------------|------------------------|
| Type of test | Vibration test |
| Specification | IEC 60068-2-6 |
| Frequency | 10-500 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.35 mm |
| Acceleration | 50.00 m/s ² |
| Test duration | 2.00 h |

Test specification

| | |
|-----------------------------------|----------------|
| Specification | IEC 63171 |
| Corrosive stress | IEC 60512-11-7 |
| Contact resistance R ₁ | 20.00 mΩ |

Test specification

| | |
|--------------|---|
| Type of test | Mechanical service life with corrosion test |
|--------------|---|

SPE-T1-M12FSF-180 - SPE PCB connector



1363337

<https://www.phoenixcontact.com/us/products/1363337>

| | |
|---------------|------------------|
| Specification | DIN EN 60512-9-1 |
|---------------|------------------|

Test specification

| | |
|--------------------------------|-------------------------|
| Type of test | Shock testing |
| Specification | IEC 60068-2-27 |
| Acceleration | 150.00 m/s ² |
| Number of shocks per direction | 2000.00 |

Mounting

| | |
|---------------|--------------|
| Mounting type | PCB mounting |
|---------------|--------------|

Processing notes

| | |
|---|--------|
| Process | Reflow |
| Moisture Sensitive Level | MSL 1 |
| Classification temperature T _c | 260 °C |
| Solder cycles in the reflow | 3 |

SPE-T1-M12FSF-180 - SPE PCB connector



1363337

<https://www.phoenixcontact.com/us/products/1363337>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002637 |
|-----------|----------|

SPE-T1-M12FSF-180 - SPE PCB connector



1363337

<https://www.phoenixcontact.com/us/products/1363337>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com