

# SACC-DSI-FS-8CON-PG 9/2,0 0,34 - Device connector rear mounting



1401267

<https://www.phoenixcontact.com/us/products/1401267>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 8-position, Socket, straight, M12, A-coding, on free cable end, Individual wires, cable length: 2 m, 0.34 mm<sup>2</sup>, TPE litz wire, potted

## Commercial data

Item number	1401267
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB24
Product key	ABQCHE
GTIN	4046356543835
Weight per piece (including packing)	83.198 g
Weight per piece (excluding packing)	80.678 g
Customs tariff number	85444290
Country of origin	DE

# SACC-DSI-FS-8CON-PG 9/2,0 0,34 - Device connector rear mounting



1401267

<https://www.phoenixcontact.com/us/products/1401267>

## Technical data

### Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

### Mounting

Mounting type	Rear mounting (Pg9, with locking nut)
Tightening torque	2 Nm ... 3 Nm

### Product properties

Product type	Circular connectors (device side)
Application	Signal
Number of positions	8
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Molding compound	PUR (potted)
Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Conductor material	Tin-plated Cu litz wires

### Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V
Nominal current $I_N$	2 A
Max. conductor resistance	80 m $\Omega$ /m

### Connection data

# SACC-DSI-FS-8CON-PG 9/2,0 0,34 - Device connector rear mounting



1401267

<https://www.phoenixcontact.com/us/products/1401267>

## Conductor connection

Connection method	Individual wires
Contact connection type	Socket
Conductor cross-section	0.34 mm <sup>2</sup>
Tightening torque	2 Nm ... 3 Nm

## Connector

### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	A

### Connection 2

Head design	free cable end
-------------	----------------

## Cable/line

Cable length	2 m
Cable type	TPE litz wire
Cable cross section	0.34 mm <sup>2</sup>
Conductor material	Tin-plated Cu litz wires
AWG signal line	22
Material wire insulation	TPE
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Cable resistance	≤ 80 mΩ/m
Cable insulation resistance	≥ 20 MΩ*km

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-25 °C ... 90 °C (cable, fixed installation)
UL Type Rating	Type 4 (indoor use only)


# SACC-DSI-FS-8CON-PG 9/2,0 0,34 - Device connector rear mounting

1401267

<https://www.phoenixcontact.com/us/products/1401267>

## Drawings

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side


# SACC-DSI-FS-8CON-PG 9/2,0 0,34 - Device connector rear mounting



1401267

<https://www.phoenixcontact.com/us/products/1401267>

Circuit diagram



Contact assignment of the M12 socket

# SACC-DSI-FS-8CON-PG 9/2,0 0,34 - Device connector rear mounting



1401267

<https://www.phoenixcontact.com/us/products/1401267>

## Classifications

### ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

### ETIM

ETIM 10.0	EC003570
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSI-FS-8CON-PG 9/2,0 0,34 - Device connector rear mounting



1401267

<https://www.phoenixcontact.com/us/products/1401267>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	3de8609f-5dc5-47cb-a24d-63bbffd5ad83

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)