

SAC-2P-100,0-915 - Bus system cable



1401361

<https://www.phoenixcontact.com/us/products/1401361>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

By the meter, Bus system cable, PROFIBUS, shielded, PUR/PVC, blue, 2-wire (1x2xAWG24/19), color single wire: red, green, cable length: 100 m



Commercial data

Item number	1401361
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF1LEA
GTIN	4046356552981
Weight per piece (including packing)	7,630 g
Weight per piece (excluding packing)	7,630 g
Customs tariff number	85444995
Country of origin	DE

SAC-2P-100,0-915 - Bus system cable

1401361

<https://www.phoenixcontact.com/us/products/1401361>

Technical data

Product properties

Product type	Data cable by the meter
Number of positions	2
Shielded	yes

Electrical properties

Transmission medium	Copper
---------------------	--------


Interfaces

Signal type/category	PROFIBUS
----------------------	----------

Cable/line

Cable length	100 m
--------------	-------

PROFIBUS [915]

Dimensional drawing	
Cable weight	74 kg/km
Number of positions	2
Shielded	yes
Cable type	PROFIBUS [915]
Conductor structure	1x2xAWG24/19
Conductor structure signal line	19x 0.14 mm
AWG signal line	24
Conductor cross-section	2x 0.25 mm ²
Wire diameter incl. insulation	2.56 mm
External cable diameter	8.00 mm ±0.4 mm
Outer sheath, material	PUR
External sheath, color	blue
Conductor material	Bare Cu litz wires
Material wire insulation	Foamed PE
Single wire, color	red, green
Thickness, outer sheath	approx. 0.80 mm
Overall twist	2 wires, twisted
Optical shield covering	70 %
Insulation resistance	≥ 16 GΩ*km

SAC-2P-100,0-915 - Bus system cable



1401361

<https://www.phoenixcontact.com/us/products/1401361>

Working capacitance	28 nF (at 1 kHz)
Nominal voltage, cable	≤ 100 V
Test voltage Core/Core	3600 V DC
Minimum bending radius, flexible installation	5 x D
Smallest bending radius, movable installation	40 mm
Dynamic load capacity (bending)	Max. bending cycles: 3000000, Bending radius: 60 mm, Acceleration: 4 m/s ²
Tensile strength	≤ 100 N
Flame resistance	according to IEC 60332-1
Resistance to oil	Resistant to mineral oils and grease
Ambient temperature (operation)	-40 °C ... 80 °C (Cable, flexible installation)

SAC-2P-100,0-915 - Bus system cable



1401361

<https://www.phoenixcontact.com/us/products/1401361>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 9.0	EC003249
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-2P-100,0-915 - Bus system cable



1401361

<https://www.phoenixcontact.com/us/products/1401361>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com