

SAC-4P-100,0-93P - Bus system cable



1401819

<https://www.phoenixcontact.com/us/products/1401819>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, Ethernet, 4-wire, shielded, PVC, blue outer sheath, 2 x 2 x 0.14 mm², cable ring: 100 m

Commercial data

Item number	1401819
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF11
Product key	AF1LFA
GTIN	4046356574129
Weight per piece (including packing)	4,975.1 g
Weight per piece (excluding packing)	4,472 g
Customs tariff number	85444995
Country of origin	DE

SAC-4P-100,0-93P - Bus system cable



1401819

<https://www.phoenixcontact.com/us/products/1401819>

Technical data

Product properties

Product type	Data cable by the meter
Number of positions	4

Electrical properties

Transmission medium	Copper
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

Interfaces

Signal type/category	Ethernet CAT5 (IEC 11801:2002)
----------------------	--------------------------------

Cable/line

Cable length	100 m
--------------	-------

Ethernet [93P]

UL AWM Style	2654 (90 °C / 300 V)
Number of positions	4
Shielded	yes
Cable type	Ethernet [93P]
Conductor structure	2x2xAWG26/7, SF/UTP
Signal runtime	0.4 ns/m
Signal speed	0.6 c
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	2x 2x 0.14 mm ²
Wire diameter incl. insulation	0.98 mm ±0.05 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	white/orange-orange, white/green-green
Thickness, outer sheath	≥ 1.00 mm
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	Two pairs with two fillers to the core
Optical shield covering	85 %
Max. conductor resistance	≤ 140 Ω/km
Insulation resistance	> 5 GΩ*km
Wave impedance	100 Ω ±5 % (at 100 MHz)
Working capacitance	< 56 nF
Nominal voltage, cable	≤ 300 V AC

SAC-4P-100,0-93P - Bus system cable



1401819

<https://www.phoenixcontact.com/us/products/1401819>

	≤ 450 V DC
Test voltage Core/Core	2500 V DC
Smallest bending radius, movable installation	25 mm
Tensile strength	≤ 40 N
Shield attenuation	32.00 dB (up to 100 MHz)
Flame resistance	According to VW-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Resistant to cleaning agents/disinfectants (According to ECOLAB F&E/P3-E No. 40-1)
Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (installation)	0 °C ... 50 °C

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation) (Cable, flexible installation)	-40 °C ... 90 °C (Cable, flexible installation)
--	---

SAC-4P-100,0-93P - Bus system cable



1401819

<https://www.phoenixcontact.com/us/products/1401819>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1401819>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00371

SAC-4P-100,0-93P - Bus system cable



1401819

<https://www.phoenixcontact.com/us/products/1401819>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 10.0	EC003249
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-100,0-93P - Bus system cable



1401819

<https://www.phoenixcontact.com/us/products/1401819>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	43.71 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com