

SACB-16X0,5/ 3X1,0-50,0 80MC - Master cable ring



1402304

<https://www.phoenixcontact.com/us/products/1402304>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Master cable for sensor/actuator boxes, 19-wire, unshielded, PUR halogen-free, drag chain and robot compatible, black outer sheath, 16 x 0.5 mm² and 3 x 1.0 mm²



Commercial data

Item number	1402304
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF45
Product key	AF3ZBX
GTIN	4046356594196
Weight per piece (including packing)	9,200 g
Weight per piece (excluding packing)	9,006 g
Customs tariff number	85444995
Country of origin	DE

SACB-16X0,5/ 3X1,0-50,0 80MC - Master cable ring

1402304

<https://www.phoenixcontact.com/us/products/1402304>

Technical data

Product properties

Product type	Cable by the meter
Application	Distributor boxes
Number of positions	19


Electrical properties

Nominal voltage U_N	300 V AC
	300 V DC

Cable/line

Cable length	50 m
--------------	------

PUR halogen-free, highly flexible [80MC]

Dimensional drawing	
Number of positions	19
Shielded	no
Cable type	PUR halogen-free, highly flexible [80MC]
Conductor structure signal line	28x 0.15 mm
AWG signal line	20
Conductor structure, voltage supply	56x 0.15 mm
AWG power supply	17
Conductor cross-section	16x 0.5 mm ² (Signal line) 3x 1 mm ² (power line)
External cable diameter	10.75 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, green/yellow, white, green, yellow, gray, pink, red, black, violet, gray/pink, red/blue, white/green, brown/green, white/yellow, yellow/brown, white/gray, gray/brown
Overall twist	Wires twisted to an optimum in two layers
Max. conductor resistance	39 Ω/km (Signal line) 19.5 Ω/m (power line)
Insulation resistance	≥ 10 MΩ*km (at 20 °C)

SACB-16X0,5/ 3X1,0-50,0 80MC - Master cable ring



1402304

<https://www.phoenixcontact.com/us/products/1402304>

Nominal voltage, cable	300 V
Test voltage	2000 V
Smallest bending radius, fixed installation	90 mm
Smallest bending radius, movable installation	120 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 120 mm, Traversing path: 5 m, Traversing rate: 3 m/s, Acceleration: 5 m/s ²
Dynamic load capacity (torsion)	Torsion: ±120 °/m, Torsion cycles: ≥3000000
Halogen-free	The cable is halogen-free
Flame resistance	DIN EN 50265-2-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	somewhat resistant to welding sparks
Special properties	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-30 °C ... 70 °C (cable, fixed installation)
	5 °C ... 70 °C (Cable, flexible installation)
	to 80 °C (in acc. with UL)

SACB-16X0,5/ 3X1,0-50,0 80MC - Master cable ring



1402304

<https://www.phoenixcontact.com/us/products/1402304>

Classifications

ECLASS

ECLASS-13.0	27060106
ECLASS-15.0	27060106

ETIM

ETIM 10.0	EC003250
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SACB-16X0,5/ 3X1,0-50,0 80MC - Master cable ring



1402304

<https://www.phoenixcontact.com/us/products/1402304>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	102.916 kg CO2e
---------	-----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com