

SAC-2P-M 8MR/0,28-PUR/CI-1L-Z - Sensor/actuator cable



1403006

<https://www.phoenixcontact.com/us/products/1403006>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 2-position, PUR halogen-free, black-gray RAL 7021, Plug angled M8, on Valve connector CI (9.4 mm), with 1 LED, Wiring: Z diode, cable length: 0.28 m

Commercial data

Item number	1403006
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1DOA
GTIN	4046356640954
Weight per piece (including packing)	28 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

SAC-2P-M 8MR/0,28-PUR/CI-1L-Z - Sensor/actuator cable



1403006

<https://www.phoenixcontact.com/us/products/1403006>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
Number of positions	2

Connection data

Connection assignment

Contact Color (signal designation) Contact (optional)	3 (M8 plug) BU 2 (Valve connector)
	4 (M8 plug) BN 1 (Valve connector)
	1 (M8 plug) N.C.

Electrical properties

Nominal voltage U_N	24 V AC
	24 V DC

Connector

Connection 1

Type	Plug angled M8
------	----------------


Connection 2

Type	Valve connector CI (9.4 mm)
Protective circuit	Z diode

Cable/line

Cable length	0.28 m
--------------	--------

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	23 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22

SAC-2P-M 8MR/0,28-PUR/CI-1L-Z - Sensor/actuator cable



1403006

<https://www.phoenixcontact.com/us/products/1403006>

Conductor cross-section	3x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.02 mm (Signal line)
External cable diameter	3.85 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation) approx. 0.50 mm (Outer cable sheath)
Overall twist	3 wires, twisted
Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	19 mm
Smallest bending radius, movable installation	38 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 38 mm, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)


SAC-2P-M 8MR/0,28-PUR/CI-1L-Z - Sensor/actuator cable

1403006

<https://www.phoenixcontact.com/us/products/1403006>


Drawings

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

Circuit diagram



Contact assignment of the M8 plug and the valve connector

SAC-2P-M 8MR/0,28-PUR/CI-1L-Z - Sensor/actuator cable





1403006


<https://www.phoenixcontact.com/us/products/1403006>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1403006>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

 EAC-RoHS Approval ID: RU D-DE.HB35.B.00387	
--	--

SAC-2P-M 8MR/0,28-PUR/CI-1L-Z - Sensor/actuator cable



1403006

<https://www.phoenixcontact.com/us/products/1403006>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-2P-M 8MR/0,28-PUR/CI-1L-Z - Sensor/actuator cable



1403006

<https://www.phoenixcontact.com/us/products/1403006>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com