

VS-M12FSBP-IP20-94B-LI/0,3 - Network cable




1403267

<https://www.phoenixcontact.com/us/products/1403267>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Network cable, degree of protection: IP67/IP20, number of positions: 8



Commercial data

Item number	1403267
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB25
Product key	ABNPAA
GTIN	4046356646215
Weight per piece (including packing)	50 g
Weight per piece (excluding packing)	44.861 g
Customs tariff number	85444210
Country of origin	PL

Technical data

Product properties

Product type	Circular connectors (device side)
Number of positions	8
Shielded	yes

Material specifications

Outer sheath, material	PUR
Conductor material	Bare Cu litz wires

Electrical properties

Transmission characteristics (category)	Class D
Wave impedance	100 Ω

Cable/line

Cable type	Ethernet
Cable structure	4x2xAWG26/7; S/FTP
External cable diameter	6.40 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Wire diameter incl. insulation	1 mm
Single wire, color	white-blue, white-orange, white-green, white-brown
Cable cross section	0.14 mm ²
Conductor material	Bare Cu litz wires
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Wave impedance	100 Ω ±15 % (at 1 ... 100 MHz)
Smallest bending radius, fixed installation	min. 32 mm (cable, fixed installation)
Smallest bending radius, movable installation	min. 32 mm (Cable, flexible installation)
Ambient temperature (operation)	-25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67/IP20
Ambient temperature (operation)	Plug / socket
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 80 °C (without mechanical actuation)
Ambient temperature (operation) (Cable, flexible installation)	-25 °C ... 80 °C (Cable, flexible installation)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

VS-M12FSBP-IP20-94B-LI/0,3 - Network cable



1403267

<https://www.phoenixcontact.com/us/products/1403267>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1403267>



EAC

Approval ID: 19060508

VS-M12FSBP-IP20-94B-LI/0,3 - Network cable



1403267

<https://www.phoenixcontact.com/us/products/1403267>

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 10.0	EC003570
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-M12FSBP-IP20-94B-LI/0,3 - Network cable



1403267

<https://www.phoenixcontact.com/us/products/1403267>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com