

# ANT-OMNI-0671-01 - Antenna

1396316

<https://www.phoenixcontact.com/us/products/1396316>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Multiband omnidirectional antenna for wall or mast mounting, 0.6 GHz ... 7.1 GHz, gain: 1 dBi ... 3 dBi, degree of protection: IP67, seawater-resistant, connection: N (female), incl. mounting bracket and mast clamps



## Your advantages

- Ideally suited for freely mobile or stationary applications in 2G/3G/4G/5G cellular networks
- Universal use with the wide frequency range
- Resistant to salt water
- Future-proof, thanks to the use of lead-free materials

## Commercial data

Item number	1396316
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN23
Product key	DNC6A2
GTIN	4063151780616
Weight per piece (including packing)	206 g
Weight per piece (excluding packing)	141 g
Customs tariff number	85177100
Country of origin	TW

# ANT-OMNI-0671-01 - Antenna



1396316

<https://www.phoenixcontact.com/us/products/1396316>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Antenna
Scope of supply	included mounting bracket and mast clamps
Radiation characteristics	Omnidirectional
Gain	2 dBi (617 MHz ... 960 MHz) 1 dBi (1.4 GHz ... 1.6 GHz) 2 dBi (1.7 GHz ... 2.7 GHz) 3 dBi (3.3 GHz ... 7.1 GHz)
Vertical beamwidth	70 ° (617 MHz ... 960 MHz) 60 ° (1.4 GHz ... 2.7 GHz) 45 ° (3.3 GHz ... 5.9 GHz) 30 ° 6.0 GHz ... 7.1 GHz
Horizontal beamwidth	360 °
Polarization	Linear vertical

### Electrical properties

Frequency band	2400 MHz 868 MHz 700 MHz 800 MHz 850 MHz 900 MHz 1700 MHz 1800 MHz 1900 MHz 2100 MHz 2600 MHz 3600 MHz 5 GHz
Frequency range	0.6 GHz ... 7.1 GHz
Impedance	50 Ω
Maximum capacity	1.00 W
Voltage standing wave ratio VSWR in a 50 Ω system	≤ 3.50

### Connection data

Connection technology


# ANT-OMNI-0671-01 - Antenna

1396316

<https://www.phoenixcontact.com/us/products/1396316>

Connection method	N (female)
Outside diameter	30 mm ... 45 mm (Mast)

## Dimensions

Dimensional drawing	
Height	158 mm
Diameter	24 mm
Hole diameter	6 mm

## External dimensions

Outside diameter	30 mm ... 45 mm (Mast)
------------------	------------------------

## Material specifications

Color	gray (RAL 7042)
Material (Radom)	Plastic (glass-fiber reinforced)
Material (Holder)	Plastic (glass-fiber reinforced)
Material (U-bolt)	Stainless steel V2A
Flammability rating according to UL 94	V0

## Cable/line

Other resistance	salt water resistant
------------------	----------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-30 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Wind velocity	220 km/h

## Standards and regulations

Other resistance	salt water resistant
------------------	----------------------

## Mounting

Mounting type	Panel mounting
	Mast mounting
Assembly note	Outdoors and indoors


# ANT-OMNI-0671-01 - Antenna

1396316

<https://www.phoenixcontact.com/us/products/1396316>

## Drawings

Dimensional drawing




Dimensional drawing

# ANT-OMNI-0671-01 - Antenna

1396316

<https://www.phoenixcontact.com/us/products/1396316>

Schematic diagram



Installation example (antenna cable and surge protection available as accessories)


# ANT-OMNI-0671-01 - Antenna

1396316

<https://www.phoenixcontact.com/us/products/1396316>




Schematic diagram



Sealing tape available as an accessory

Diagram



960 MHz directional characteristics


# ANT-OMNI-0671-01 - Antenna



1396316


<https://www.phoenixcontact.com/us/products/1396316>

## Diagram




2700 MHz directional characteristics

## Diagram



3800 MHz directional characteristics

## Diagram



5925 MHz directional characteristics

# ANT-OMNI-0671-01 - Antenna



1396316

<https://www.phoenixcontact.com/us/products/1396316>

## Classifications

### ECLASS

ECLASS-13.0	19070105
ECLASS-15.0	19070105

### ETIM

ETIM 10.0	EC001698
-----------	----------

### UNSPSC

UNSPSC 21.0	43223100
-------------	----------

# ANT-OMNI-0671-01 - Antenna



1396316

<https://www.phoenixcontact.com/us/products/1396316>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	6.047 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)