

# SAC-5P-M12T/2XM12 FF VA - Bus system T-connector



1403898

<https://www.phoenixcontact.com/us/products/1403898>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system T-connector, 5-position, unshielded, Plug straight M12, coding: A, on Socket straight M12, coding: A, PIN 2+4 bridged and Socket straight M12, coding: A, PIN 2+4 bridged, Special wiring

## Commercial data

Item number	1403898
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF10
Product key	AF1GAA
GTIN	4046356676137
Weight per piece (including packing)	28.4 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85366990
Country of origin	DE

# SAC-5P-M12T/2XM12 FF VA - Bus system T-connector



1403898

<https://www.phoenixcontact.com/us/products/1403898>

## Technical data

### Product properties

Product type	T-distributor
Number of positions	5
No. of cable outlets	2
Shielded	no
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	60 V
Nominal current $I_N$	4 A

### Signaling

Status display	no
Status display present	no

### Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Stainless steel

### Connector

#### Connection 1

Type	Plug straight M12
Coding type	A

#### Connection 2

Type	Socket straight M12
Coding type	A

#### Connection 3

Type	Socket straight M12
Coding type	A

# SAC-5P-M12T/2XM12 FF VA - Bus system T-connector



1403898

<https://www.phoenixcontact.com/us/products/1403898>

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

## Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101


# SAC-5P-M12T/2XM12 FF VA - Bus system T-connector

1403898

<https://www.phoenixcontact.com/us/products/1403898>

## Drawings

Dimensional drawing



M12 T-distributor

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

# SAC-5P-M12T/2XM12 FF VA - Bus system T-connector

1403898

<https://www.phoenixcontact.com/us/products/1403898>

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

# SAC-5P-M12T/2XM12 FF VA - Bus system T-connector



1403898

<https://www.phoenixcontact.com/us/products/1403898>

## Classifications

### ECLASS

ECLASS-13.0	27440106
ECLASS-15.0	27440106

### ETIM

ETIM 10.0	EC002925
-----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

# SAC-5P-M12T/2XM12 FF VA - Bus system T-connector



1403898

<https://www.phoenixcontact.com/us/products/1403898>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)