

# SAC-5P-100,0-923 - Cable reel



1400493

<https://www.phoenixcontact.com/us/products/1400493>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, CANopen®, DeviceNet™, shielded, PUR halogen-free, silver-gray RAL 7001, 4-wire (2xAWG24/19+2xAWG22/19), color single wire: red-black, blue-white, cable length: 100 m

## Commercial data

Item number	1400493
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF11
Product key	AF1LEA
GTIN	4046356497626
Weight per piece (including packing)	5,808.4 g
Weight per piece (excluding packing)	5,731.5 g
Customs tariff number	85444995
Country of origin	DE

# SAC-5P-100,0-923 - Cable reel

1400493

<https://www.phoenixcontact.com/us/products/1400493>

## Technical data

### Product properties

Product type	Cable by the meter
Sensor type	CANopen®
Number of positions	4


### Interfaces

Signal type/category	CANopen®
	DeviceNet™

### Cable/line

Cable length	100 m
--------------	-------

CANopen®/DeviceNet™, PUR, gray [923]

Dimensional drawing	
UL AWM Style	21198 (80°C/300 V)
Number of positions	4
Shielded	yes
Cable type	CANopen®/DeviceNet™, PUR, gray [923]
Conductor structure	2xAWG24/19+2xAWG22/19
AWG signal line	24
AWG power supply	22
Conductor cross-section	2x 0.25 mm <sup>2</sup> (Data cable) 2x 0.34 mm <sup>2</sup> (Power supply) 1x 0.34 mm <sup>2</sup> (Drain wire)
Wire diameter incl. insulation	1.95 mm ±0.05 mm (Data cable) 1.4 mm ±0.05 mm (Power supply)
External cable diameter	6.70 mm ±0.3 mm
Outer sheath, material	PUR
External sheath, color	silver-gray RAL 7001
Conductor material	Tin-plated Cu litz wires
Material wire insulation	Foamed PE (Data cable) PE (Power supply)
Single wire, color	red-black, blue-white
Twisted pairs	2 cores to the pair
Overall twist	2 pairs around a drain wire in the center to the core

# SAC-5P-100,0-923 - Cable reel



1400493

<https://www.phoenixcontact.com/us/products/1400493>

Optical shield covering	80 %
Insulation resistance	≥ 5 GΩ*km (Data cable)
	≥ 5 GΩ*km (Power supply)
Wave impedance	120 Ω ±10 % (with 1 MHz)
Nominal voltage, cable	≤ 300 V (Peak value, not for high-power applications)
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 70 mm, Bending radius: 15 x D, Traversing path: 4.5 m, Traversing rate: 3 m/s, Acceleration: 3 m/s <sup>2</sup> , Ambient temperature: -20 °C ... 60 °C
Shield attenuation	≤ 22.9 dB/km (with 1 MHz)
	≤ 16.4 dB/km (At 500 kHz)
	≤ 9.5 dB/km (At 125 kHz)
Halogen-free	in accordance with DIN VDE 0472 part 815
	according to IEC 60754-1
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
	IEC 60332-1-2
Ambient temperature (operation)	in accordance with ISO 6722-1 5.22 (UN ECE-R 118.01)
	-40 °C ... 80 °C (cable, fixed installation)
	-30 °C ... 70 °C (Cable, flexible installation)
	-20 °C ... 60 °C (for installation)
	-20 °C ... 60 °C (cable, drag chain applications)

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	-20 °C ... 70 °C (Cable, flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C

# SAC-5P-100,0-923 - Cable reel



1400493

<https://www.phoenixcontact.com/us/products/1400493>

## Classifications

### ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

### ETIM

ETIM 10.0	EC003249
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-5P-100,0-923 - Cable reel



1400493

<https://www.phoenixcontact.com/us/products/1400493>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)