

SAC-3P-M 8MS/ 1,3-PUR/4P-M 8FS - Sensor/actuator cable



1400509

<https://www.phoenixcontact.com/us/products/1400509>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M8, coding: A, on Socket straight M8, cable length: 1.3 m

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1400509 |
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| Product key | AF1BBA |
| GTIN | 4046356499149 |
| Weight per piece (including packing) | 35.445 g |
| Weight per piece (excluding packing) | 35.445 g |
| Country of origin | DE |

SAC-3P-M 8MS/ 1,3-PUR/4P-M 8FS - Sensor/actuator cable



1400509

<https://www.phoenixcontact.com/us/products/1400509>

Technical data

Product properties

| | |
|----------------------|-----------------------|
| Product type | Sensor/actuator cable |
| Number of positions | 3 |
| No. of cable outlets | 1 |
| Shielded | no |
| Coding | A |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 | HB |
| Seal material | NBR |
| Material of grip body | TPU, hardly inflammable, self-extinguishing |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | TPU GF |
| Material for screw connection | Zinc die-cast, nickel-plated |

Electrical properties

| | |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |
| Nominal current I_N | 4 A |

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Connector

Connection 1

| | |
|---------------------|------------------|
| Type | Plug straight M8 |
| Number of positions | 3 |
| Coding type | A |

Connection 2

| | |
|---------------------|--------------------|
| Type | Socket straight M8 |
| Number of positions | 3 |

Cable/line

| | |
|--------------|-------|
| Cable length | 1.3 m |
|--------------|-------|


SAC-3P-M 8MS/ 1,3-PUR/4P-M 8FS - Sensor/actuator cable



1400509

<https://www.phoenixcontact.com/us/products/1400509>

PUR halogen-free black [PUR]

| | |
|---|---|
| Dimensional drawing |  |
| Cable weight | 23 kg/km |
| UL AWM Style | 20549 / 10493 (80°C/300 V) |
| Number of positions | 4 |
| Shielded | no |
| Cable type | PUR halogen-free black [PUR] |
| Conductor structure signal line | 32x 0.10 mm |
| AWG signal line | 24 |
| Conductor cross-section | 4x 0.25 mm ² (Signal line) |
| Wire diameter incl. insulation | 1.17 mm ±0.02 mm (Signal line) |
| External cable diameter | 3.95 mm ±0.15 mm |
| Outer sheath, material | PUR |
| External sheath, color | black-gray RAL 7021 |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PP |
| Single wire, color | brown, white, blue, black |
| Thickness, insulation | ≥ 0.21 mm (Core insulation) approx. 0.50 mm (Outer cable sheath) |
| Overall twist | 4 wires, twisted |
| Max. conductor resistance | max. 78 Ω/km (at 20 °C) |
| Insulation resistance | ≥ 100 GΩ*km (at 20 °C) |
| Nominal voltage, cable | ≤ 300 V |
| Test voltage | ≥ 3000 V |
| Smallest bending radius, fixed installation | 20 mm |
| Smallest bending radius, movable installation | 40 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 10000000, Bending radius: 44 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 5 m/s ² |
| Dynamic load capacity (torsion) | Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min. |
| Halogen-free | in accordance with DIN VDE 0472 part 815 |
| Flame resistance | in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s) |
| Resistance to oil | in accordance with DIN EN 60811-2-1 |
| Other resistance | Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant |

SAC-3P-M 8MS/ 1,3-PUR/4P-M 8FS - Sensor/actuator cable



1400509

<https://www.phoenixcontact.com/us/products/1400509>

| | |
|---------------------------------|---|
| Special properties | partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) |
| | Flexible cable conduit capable |
| | Silicone-free |
| Ambient temperature (operation) | Free of substances which would hinder coating with paint or varnish |
| | -40 °C ... 80 °C (cable, fixed installation) |
| | -25 °C ... 80 °C (Cable, flexible installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|--|
| Degree of protection | IP65 |
| | IP67 |
| | IP68 |
| Ambient temperature (operation) | -25 °C ... 90 °C (Plug / socket) |
| | -40 °C ... 80 °C (cable, fixed installation) |
| | -5 °C ... 80 °C (Cable, flexible installation) |

SAC-3P-M 8MS/ 1,3-PUR/4P-M 8FS - Sensor/actuator cable

1400509

<https://www.phoenixcontact.com/us/products/1400509>

Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Dimensional drawing



Socket M8 x 1, straight

SAC-3P-M 8MS/ 1,3-PUR/4P-M 8FS - Sensor/actuator cable

1400509


<https://www.phoenixcontact.com/us/products/1400509>

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

SAC-3P-M 8MS/ 1,3-PUR/4P-M 8FS - Sensor/actuator cable



1400509

<https://www.phoenixcontact.com/us/products/1400509>

Circuit diagram



SAC-3P-M 8MS/ 1,3-PUR/4P-M 8FS - Sensor/actuator cable



1400509

<https://www.phoenixcontact.com/us/products/1400509>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com