

# VS-PPC-C1-RJ45-POBK-PG9-4Q5-OL - RJ45 connector



1404142

<https://www.phoenixcontact.com/us/products/1404142>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, degree of protection: IP65/IP67, number of positions: 4, CAT5 (IEC 11801:2002), material: Plastic, connection method: IDC fast connection, connection cross section: AWG 26- 22, cable outlet: straight, color: black

## Commercial data

Item number	1404142
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABNOAA
GTIN	4046356303699
Weight per piece (including packing)	33 g
Weight per piece (excluding packing)	29.74 g
Country of origin	DE

# VS-PPC-C1-RJ45-POBK-PG9-4Q5-OL - RJ45 connector



1404142

<https://www.phoenixcontact.com/us/products/1404142>

## Technical data

### Product properties

Product type	Data connector (cable side)
Type	RJ45
Number of positions	4
Connection profile	RJ45 8(4)
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Contact resistance	0.001 $\Omega$ (Wire – IDC) 0.005 $\Omega$ (Litz wires – IDC)
Transmission medium	Copper
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

### Connection data

#### Connection technology

Connection method	IDC fast connection
Connection cross section AWG	26 ... 22 (solid) 26 ... 22 (flexible)
Conductor cross-section	0.13 mm <sup>2</sup> ... 0.32 mm <sup>2</sup> (solid) 0.14 mm <sup>2</sup> ... 0.36 mm <sup>2</sup> (flexible)

### Dimensions

Width	22 mm
Height	30 mm
Length	57.7 mm

### Material specifications

Color	black
Flammability rating according to UL 94	V0
Housing material	Plastic
Cable seal material	TPE
Contact material	Copper alloy
Contact surface material	Gold over nickel

# VS-PPC-C1-RJ45-POBK-PG9-4Q5-OL - RJ45 connector



1404142

<https://www.phoenixcontact.com/us/products/1404142>

Contact carrier material	PC
O-ring material	NBR

## Cable/line

External cable diameter	5 mm ... 8 mm
Cable cross section	0.14 mm <sup>2</sup>

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C

## Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

# VS-PPC-C1-RJ45-POBK-PG9-4Q5-OL - RJ45 connector



1404142

<https://www.phoenixcontact.com/us/products/1404142>

## Classifications

### ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

### ETIM

ETIM 10.0	EC002636
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-PPC-C1-RJ45-POBK-PG9-4Q5-OL - RJ45 connector



1404142

<https://www.phoenixcontact.com/us/products/1404142>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) 2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	f3c2abbd-7466-4ddc-845a-bfbb2b874763

### EF3.1 Climate Change

CO2e kg	1.324 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)