

# VS-M12FSBPS-IP20-93E-LI/0,5 - Device connector rear mounting



1404205

<https://www.phoenixcontact.com/us/products/1404205>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, degree of protection: IP67/IP20, cable length: 0.5 m, number of positions: 4, 100 Mbps, CAT5, cable outlet: straight, Ethernet, 2x2xAWG26/7, SF/UTP, water blue RAL 5021

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1404205       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB18          |
| Product key                          | ABNPAB        |
| GTIN                                 | 4046356681490 |
| Weight per piece (including packing) | 58 g          |
| Weight per piece (excluding packing) | 49.884 g      |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# VS-M12FSBPS-IP20-93E-LI/0,5 - Device connector rear mounting



1404205

<https://www.phoenixcontact.com/us/products/1404205>

## Technical data

### Product properties

|                      |                                   |
|----------------------|-----------------------------------|
| Product type         | Circular connectors (device side) |
| Application          | Data                              |
|                      | On the device side                |
| Type                 | M12                               |
| Sensor type          | Ethernet                          |
| Number of positions  | 4                                 |
| No. of cable outlets | 1                                 |
| Shielded             | yes                               |
| Cable outlet         | straight                          |

### Material specifications

|  |                    |
|--|--------------------|
| Flammability rating according to UL 94 | V0                 |
| Seal material, flat gasket             | FKM                |
| Outer sheath, material                 | PUR                |
| Conductor material                     | Bare Cu litz wires |

### Electrical properties

|   |  |
|---|--|
| Nominal voltage $U_N$                   | 48 V   |
| Nominal current $I_N$                   | 2 A (Plug/socket in accordance with IEC 61076-2-101, cable technical data is to be observed) |
| Transmission medium                     | Copper   |
| Transmission speed                      | 100 Mbps   |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002)  |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Connector

#### Connection 1

|                      |  |
|----------------------|--|
| Type                 | Flush-type female connector straight M12 |
| Locking type         | SPEEDCON                                 |
| Coding type          | D  |
| Degree of protection | IP65/IP67                                |

#### Connection 2

|                      |                    |
|----------------------|--------------------|
| Type                 | Plug straight RJ45 |
| Degree of protection | IP20               |

# VS-M12FSBPS-IP20-93E-LI/0,5 - Device connector rear mounting


1404205

<https://www.phoenixcontact.com/us/products/1404205>

## Cable/line

|              |        |
|--------------|--------|
| Cable length | 0.50 m |
|--------------|--------|

### Ethernet flexible CAT5, 2-pair [93E]

|                                 |  |
|---------------------------------|--|
| Dimensional drawing             |  |
| Cable weight                    | 42 kg/km   |
| UL AWM Style                    | 20963 (80°C/30 V)  |
| Wiring standards/regulations    | Electrical requirements EN 50288-2-2   |
| Number of positions             | 4  |
| Shielded                        | yes  |
| Cable type                      | Ethernet flexible CAT5, 2-pair [93E]   |
| Conductor structure             | 2x2xAWG26/7, SF/UTP  |
| Signal runtime                  | 5.3 ns/m   |
| Conductor structure signal line | 7x 0.16 mm   |
| AWG signal line                 | 26   |
| Conductor cross-section         | 2x 2x 0.14 mm <sup>2</sup>   |
| Wire diameter incl. insulation  | 0.98 mm  |
| External cable diameter         | 6.40 mm ±0.2 mm  |
| Outer sheath, material          | PUR  |
| External sheath, color          | water blue RAL 5021  |
| Conductor material              | Bare Cu litz wires   |
| Material wire insulation        | Foamed PE  |
| Single wire, color              | white/orange-orange, white/green-green   |
| Thickness, outer sheath         | 1.20 mm  |
| Twisted pairs                   | 2 cores to the pair  |
| Overall twist                   | Two pairs with two fillers to the core   |
| Optical shield covering         | 70 %   |
| Insulation resistance           | ≥ 500 MΩ*km  |
| Coupling resistance             | ≤ 100.00 mΩ/m (at 10 MHz)  |
| Loop resistance                 | ≤ 290.00 Ω/km  |
| Wave impedance                  | 100 Ω ±5 Ω (at 100 MHz)  |
| Cable capacity                  | approx. 45 nF/km (at 1 kHz)  |
| Nominal voltage, cable          | ≤ 100 V (Peak value, not for high-power applications)                              |
| Test voltage Core/Core          | 700 V (50 Hz, 1 min.)  |
| Test voltage Core/Shield        | 700.00 V (50 Hz, 1 min.)   |

# VS-M12FSBPS-IP20-93E-LI/0,5 - Device connector rear mounting



1404205

<https://www.phoenixcontact.com/us/products/1404205>

|  |                                      |
|--|--------------------------------------|
| Current carrying capacity of cable                     | 2.00 A (according to DIN VDE 0891-1) |
| Minimum bending radius, fixed installation             | 4 x D                                |
| Minimum bending radius, flexible installation          | 8 x D                                |
| Smallest bending radius, fixed installation            | 26 mm                                |
| Smallest bending radius, movable installation          | 52 mm                                |
| Tensile strength                                       | ≤ 80 N                               |
| Near end crosstalk attenuation (NEXT)                  | 65.3 dB (with 1 MHz)                 |
|  | 56.3 dB (at 4 MHz)                   |
|  | 50.3 dB (at 10 MHz)                  |
|  | 47.2 dB (at 16 MHz)                  |
|  | 45.8 dB (at 20 MHz)                  |
|  | 42.9 dB (at 31.25 MHz)               |
|  | 38.4 dB (at 62.5 MHz)                |
|  | 35.3 dB (at 100 MHz)                 |
| Power-summated near end crosstalk attenuation (PSNEXT) | 62.3 dB (with 1 MHz)                 |
|  | 53.3 dB (at 4 MHz)                   |
|  | 47.3 dB (at 10 MHz)                  |
|  | 44.2 dB (at 16 MHz)                  |
|  | 42.8 dB (at 20 MHz)                  |
|  | 39.9 dB (at 31.25 MHz)               |
|  | 35.4 dB (at 62.5 MHz)                |
|  | 32.3 dB (at 100 MHz)                 |
| Return attenuation (RL)                                | 23 dB (at 4 MHz)                     |
|  | 24.1 dB (at 8 MHz)                   |
|  | 25 dB (at 10 MHz)                    |
|  | 25 dB (at 16 MHz)                    |
|  | 25 dB (at 20 MHz)                    |
|  | 23.6 dB (at 31.25 MHz)               |
|  | 21.5 dB (at 62.5 MHz)                |
|  | 20.1 dB (at 100 MHz)                 |
| Shield attenuation                                     | 3.2 dB (with 1 MHz)                  |
|  | 6 dB (at 4 MHz)                      |
|  | 9.5 dB (at 10 MHz)                   |
|  | 12.1 dB (at 16 MHz)                  |
|  | 13.6 dB (at 20 MHz)                  |
|  | 17.1 dB (at 31.25 MHz)               |
|  | 24.8 dB (at 62.5 MHz)                |
|  | 32 dB (at 100 MHz)                   |
| Halogen-free   | according to IEC 60754-1             |
| Flame resistance                                       | according to IEC 60332-1-2           |
|  | in acc. to UL VW1                    |
|  | in accordance with UN ECE-R 118.03   |

# VS-M12FSBPS-IP20-93E-LI/0,5 - Device connector rear mounting



1404205

<https://www.phoenixcontact.com/us/products/1404205>

|                                    |   |
|------------------------------------|---|
| Resistance to oil                  | in accordance with EN 60811-2-1                 |
| Ambient temperature (operation)    | -40 °C ... 80 °C (cable, fixed installation)    |
|                                    | -20 °C ... 80 °C (Cable, flexible installation) |
| Ambient temperature (installation) | -20 °C ... 80 °C                                |

## Environmental and real-life conditions

### Ambient conditions

|                                 |   |
|---------------------------------|---|
| Degree of protection            | IP67/IP20                                       |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)    |
|                                 | -20 °C ... 80 °C (Cable, flexible installation) |

## Standards and regulations

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M12 circular connector       |
| Standards/specifications | according to IEC 61076-2-101 |

# VS-M12FSBPS-IP20-93E-LI/0,5 - Device connector rear mounting



1404205

<https://www.phoenixcontact.com/us/products/1404205>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1404205>



**EAC**

Approval ID: 19060508

# VS-M12FSBPS-IP20-93E-LI/0,5 - Device connector rear mounting



1404205

<https://www.phoenixcontact.com/us/products/1404205>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440103 |
| ECLASS-15.0 | 27440103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003570 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# VS-M12FSBPS-IP20-93E-LI/0,5 - Device connector rear mounting



1404205

<https://www.phoenixcontact.com/us/products/1404205>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)