

# SAC-3P-10,0-PVC/M 8FS BK VA - Sensor/actuator cable



1401474

<https://www.phoenixcontact.com/us/products/1401474>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black RAL 9005, free cable end, on Socket straight M8, coding: A, cable length: 10 m

## Commercial data

Item number	1401474
Packing unit	1 pc
Minimum order quantity	25 pc
Note	Made to order (non-returnable)
Product key	AF1BBA
GTIN	4046356557351
Weight per piece (including packing)	251.6 g
Weight per piece (excluding packing)	250 g
Country of origin	PL

# SAC-3P-10,0-PVC/M 8FS BK VA - Sensor/actuator cable



1401474

<https://www.phoenixcontact.com/us/products/1401474>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Stainless steel

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	4 A

### Signaling

Status display	no
Status display present	no

### Connector

#### Connection 1

Type	free cable end
------	----------------

#### Connection 2

Type	Socket straight M8
Number of positions	3
Coding type	A

### Cable/line

Cable length	10 m
--------------	------

PVC black [PVC]

# SAC-3P-10,0-PVC/M 8FS BK VA - Sensor/actuator cable



1401474

<https://www.phoenixcontact.com/us/products/1401474>

Dimensional drawing	
Cable weight	29 kg/km
Number of positions	3
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	3x 0.25 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.25 mm ±0.02 mm
External cable diameter	4.40 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	3 wires, twisted
Max. conductor resistance	max. 78 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≥ 300 V
Test voltage	≤ 3000 V
Flame resistance	As per UL-Style 2464
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
	IP68
	IP69K
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


# SAC-3P-10,0-PVC/M 8FS BK VA - Sensor/actuator cable

1401474

<https://www.phoenixcontact.com/us/products/1401474>


## Drawings

Dimensional drawing




Socket M8 x 1, straight

Dimensional drawing



Schematic diagram



Pin assignment M8 socket, 3-pos., view female side


# SAC-3P-10,0-PVC/M 8FS BK VA - Sensor/actuator cable



1401474

<https://www.phoenixcontact.com/us/products/1401474>

Circuit diagram



Contact assignment of M8 socket

# SAC-3P-10,0-PVC/M 8FS BK VA - Sensor/actuator cable



1401474

<https://www.phoenixcontact.com/us/products/1401474>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-3P-10,0-PVC/M 8FS BK VA - Sensor/actuator cable



1401474

<https://www.phoenixcontact.com/us/products/1401474>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)