

NS 15 UNPERF 2000MM VPE 10 - DIN rail, unperforated



1401695

<https://www.phoenixcontact.com/us/products/1401695>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver-colored

Your advantages

- All DIN rails are also available cut to length
- Particular attention has been paid to high dimensional accuracy and surface tempering
- The design of the DIN rails corresponds to European standard EN 60715

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1401695 |
| Packing unit | 10 m |
| Minimum order quantity | 20 m |
| Sales key | BE72 |
| Product key | BE7214 |
| GTIN | 4017918020507 |
| Weight per piece (including packing) | 348 g |
| Weight per piece (excluding packing) | 348 g |
| Customs tariff number | 72166190 |
| Country of origin | DE |

NS 15 UNPERF 2000MM VPE 10 - DIN rail, unperforated

1401695


<https://www.phoenixcontact.com/us/products/1401695>

Technical data

Product properties

| | |
|--------------|----------|
| Product type | DIN rail |
|--------------|----------|

Dimensions

| | |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width | 15 mm |
| Depth | 5 mm |
| Length | 2000 mm |

Material specifications

| | |
|----------|-------------------------------------------|
| Color | silver-colored |
| Material | Steel |
| Coating | galvanized, passivated with a thick layer |

Standards and regulations

| | |
|----------------------------------|------------------|
| Connection in acc. with standard | IEC / EN |
| Tests | acc. to EN 60715 |

Electrical tests

| | |
|----------------------------------|--------------------|
| Short-time withstand current | |
| Equivalent E-Cu cross-section | 10 mm ² |
| Short-time current resistance 1s | 1.2 kA |

NS 15 UNPERF 2000MM VPE 10 - DIN rail, unperforated




1401695

<https://www.phoenixcontact.com/us/products/1401695>

Drawings

Dimensional drawing



NS 15 UNPERF 2000MM VPE 10 - DIN rail, unperforated



1401695

<https://www.phoenixcontact.com/us/products/1401695>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400602 |
| ECLASS-15.0 | 27400602 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001285 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

NS 15 UNPERF 2000MM VPE 10 - DIN rail, unperforated



1401695

<https://www.phoenixcontact.com/us/products/1401695>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 1.16 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com