

# VS-ASI-FC-PVC-UL-BK/1000 - Flat cable



1404870

<https://www.phoenixcontact.com/us/products/1404870>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



AS-Interface PVC flat conductor with UL in black, for additional power supply, 2 x 1.5 mm<sup>2</sup>, 1000 m on an one-way drum

## Commercial data

Item number	1404870
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF11
Product key	AF1LFA
GTIN	4046356327602
Weight per piece (including packing)	222.22 g
Weight per piece (excluding packing)	222.22 g
Customs tariff number	85444995
Country of origin	DE

1404870

<https://www.phoenixcontact.com/us/products/1404870>

## Technical data

### Product properties

Product type	Data cable by the meter
Sensor type	AS-Interface
Number of positions	2
Shielded	no

### Electrical properties

Rated voltage (III/3)	48 V
Rated surge voltage	2 kV

### Interfaces

Signal type/category	AS-Interface
----------------------	--------------

### Dimensions

Width	10 mm
Height	4 mm

### Cable/line

Cable length	1000 m
Cable weight	73 kg/km
Number of positions	2
Shielded	no
Conductor structure	2 x 1.5 mm <sup>2</sup>
Conductor type	Flat cable
Conductor structure, voltage supply	84x 0.15 mm
AWG power supply	16
Conductor cross-section	1.5 mm <sup>2</sup>
Wire diameter incl. insulation	2.5 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	TPE
Single wire, color	brown, blue
Thickness, insulation	approx. 0.50 mm
Max. conductor resistance	≤ 13.7 Ω/km
Insulation resistance	≥ 1 MΩ*km
Nominal voltage, cable	48 V
Test voltage	2000 V
Smallest bending radius, fixed installation	≥ 6 mm (one-time)
Dynamic load capacity (bending)	Max. bending cycles: 8000000, Bending radius: 75 mm, Traversing direction: horizontal, above the broadside, Traversing rate: 4 m/s, Acceleration: 4 m/s <sup>2</sup>

# VS-ASI-FC-PVC-UL-BK/1000 - Flat cable



1404870

<https://www.phoenixcontact.com/us/products/1404870>

	Max. bending cycles: 10000000, Bending radius: 50 mm, Traversing direction: vertical, above the broadside
Halogen-free	no
Flame resistance	UL 1581, Sec. 1061 (Cable Flame)
	UL 1581, Sec. 1060 (FT-1)
	UL 1685 (CSA FT 4)
	IEC 60332-1-2
Resistance to oil	UL 1581, Sec. 480 (60 °C)
Other resistance	UV resistant
Special properties	UL type CL2 accord. to UL 13 and NEC Article 725
	UL type CMG accord. to UL 444 and NEC Article 800
Ambient temperature (operation)	-30 °C ... 90 °C (cable, fixed installation)
	-20 °C ... 90 °C (Cable, flexible installation)

## FO cable

Transmission medium	Copper
---------------------	--------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-30 °C ... 90 °C (fixed routing)
	-20 °C ... 90 °C (Flexibly installed)
Ambient temperature (storage/transport)	-30 °C ... 90 °C
Ambient temperature (assembly)	-20 °C ... 90 °C

# VS-ASI-FC-PVC-UL-BK/1000 - Flat cable



1404870

<https://www.phoenixcontact.com/us/products/1404870>

## Classifications

### UNSPSC

UNSPSC 21.0	26121707
-------------	----------

# VS-ASI-FC-PVC-UL-BK/1000 - Flat cable



1404870

<https://www.phoenixcontact.com/us/products/1404870>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)