

SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable



1402422

<https://www.phoenixcontact.com/us/products/1402422>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 17-pos., PUR/PVC, RAL 9005 (black), shielded, straight M12 SPEEDCON male plug (A-coded) to straight M12 SPEEDCON female plug, cable length: 10 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Save time, thanks to installation with SPEEDCON fast locking system
- Save space – with high-pos. connectors
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1402422 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF03 |
| Product key | AF1CNA |
| GTIN | 4046356615426 |
| Weight per piece (including packing) | 1,116 g |
| Weight per piece (excluding packing) | 1,099 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable



1402422

<https://www.phoenixcontact.com/us/products/1402422>

Technical data

Product properties

| | |
|----------------------|-----------------------|
| Product type | Sensor/actuator cable |
| Application | Standard |
| Number of positions | 17 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Coding | A |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 | V0 |
| Material of grip body | TPU, hardly inflammable, self-extinguishing |
| Contact material | CuZn |
| Contact surface material | Ni/Au |
| Contact carrier material | PA 6.6 |
| Material for screw connection | Zinc die-cast, nickel-plated |

Electrical properties

| | |
|-----------------------|---------|
| Nominal voltage U_N | 30 V AC |
| | 30 V DC |
| Nominal current I_N | 1.5 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|------------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|------------|

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Connector

Connection 1

| | |
|---------------------|----------------------------|
| Type | Plug straight M12 SPEEDCON |
| Number of positions | 17 |
| Locking type | SPEEDCON |
| Coding type | A |

Connection 2

| | |
|------|------------------------------|
| Type | Socket straight M12 SPEEDCON |
|------|------------------------------|

SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable



1402422

<https://www.phoenixcontact.com/us/products/1402422>

| | |
|---------------------|----------|
| Number of positions | 17 |
| Locking type | SPEEDCON |
| Coding type | A |

Cable/line

| | |
|--------------|------|
| Cable length | 10 m |
|--------------|------|

Black PUR/PVC twisted pair [35T]

| | |
|---|---|
| Dimensional drawing |  |
| Cable weight | 105 kg/km |
| UL AWM Style | 20233 / 1061 (80°C/300 V) |
| Number of positions | 17 |
| Shielded | yes |
| Cable type | Black PUR/PVC twisted pair [35T] |
| Conductor structure signal line | 18x 0.10 mm |
| AWG signal line | 26 |
| Conductor cross-section | 17x 0.14 mm ² (Signal line) |
| Wire diameter incl. insulation | 1 mm ±0.05 mm (Signal line) |
| External cable diameter | 9.20 mm ±0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | black RAL 9005 |
| Conductor material | Tin-plated Cu litz wires |
| Material wire insulation | PVC |
| Single wire, color | white-brown, green-yellow, gray-pink, blue-red, black-violet, gray/pink-red/blue, white/green-brown/green, white/yellow-yellow/brown-white/gray |
| Overall twist | 7 pairs and 1 three-way unit, intertwisted |
| Optical shield covering | 85 % |
| Max. conductor resistance | 142 Ω/km (at 20 °C) |
| Insulation resistance | ≥ 10 MΩ*km (at 20 °C) |
| Nominal voltage, cable | 42 V AC |
| Test voltage | 1500 V AC |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 10 x D |
| Smallest bending radius, fixed installation | 46 mm |
| Smallest bending radius, movable installation | 92 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 4000000, Bending radius: 92 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 |

SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable



1402422

<https://www.phoenixcontact.com/us/products/1402422>

| | |
|---------------------------------|--|
| | m/s ² |
| Flame resistance | According to DIN EN 60332-1-2 According to VW-1 |
| Resistance to oil | in accordance with DIN EN 60811-2-1 |
| Other resistance | hydrolysis and microbe resistant (in accordance with EN 50396) |
| Special properties | Flexible cable conduit capable |
| Ambient temperature (operation) | -30 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP65 IP67 |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket) |
| Ambient temperature (operation) (Cable, fixed installation) | -40 °C ... 80 °C (cable, fixed installation) |
| Ambient temperature (operation) (Cable, flexible installation) | -5 °C ... 80 °C (Cable, flexible installation) |

Standards and regulations

M12

| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |

SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable

1402422

<https://www.phoenixcontact.com/us/products/1402422>

Drawings

Dimensional drawing



M12 SPEEDCON plug, straight, shielded

Dimensional drawing



Socket M12-SPEEDCON, straight, shielded

SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable

1402422


<https://www.phoenixcontact.com/us/products/1402422>

Schematic diagram



Pin assignment M12 male connector, 17-pos., male side view

Schematic diagram



Pin assignment M12, 17-pos., socket side view


SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable



1402422

<https://www.phoenixcontact.com/us/products/1402422>

Circuit diagram



Contact assignment of the M12 plug


SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable



1402422

<https://www.phoenixcontact.com/us/products/1402422>

Circuit diagram



Contact assignment of the M12 socket

SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable




1402422

<https://www.phoenixcontact.com/us/products/1402422>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1402422>

|  UL Listed Approval ID: E221474 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 30 V | 1 A | - | - |

SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable



1402422

<https://www.phoenixcontact.com/us/products/1402422>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-17P-MS/10,0-35T/FS SH SCO - Sensor/actuator cable



1402422

<https://www.phoenixcontact.com/us/products/1402422>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|----------------|
| CO2e kg | 15.513 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com