

SACC-DSI-FS-4P/0,2 D-SUC - Panel feed-through



1402529

<https://www.phoenixcontact.com/us/products/1402529>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator flush-type socket, 4-pos., M12 SPEEDCON, rear/screw mounting with Pg9 thread, with 0.5 m TPE litz wire, 4 x 0.34 mm², to MC 1,5/ 3-STF-3,81

Commercial data

Item number	1402529
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABQSAA
GTIN	4046356622127
Weight per piece (including packing)	20.8 g
Weight per piece (excluding packing)	20.8 g
Country of origin	DE

Technical data

Product properties

Number of positions	4
No. of cable outlets	1
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Nominal voltage U_N	250 V
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
	-25 °C ... 90 °C (cable, fixed installation)

SACC-DSI-FS-4P/0,2 D-SUC - Panel feed-through



1402529

<https://www.phoenixcontact.com/us/products/1402529>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-FS-4P/0,2 D-SUC - Panel feed-through



1402529

<https://www.phoenixcontact.com/us/products/1402529>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com