

# VS-OE-OE-93J/100,0 - Data cable



1402832

<https://www.phoenixcontact.com/us/products/1402832>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

By the meter, Data cable, PROFINET CAT5 (100 Mbps), shielded, PUR/FRNC, red, 4-wire (1x4xAWG22/7, SF/TQ), color single wire: white, yellow, blue, orange, cable length: 100 m



## Commercial data

Item number	1402832
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	AF1LEA
GTIN	4046356650113
Weight per piece (including packing)	6,275 g
Weight per piece (excluding packing)	6,275 g
Country of origin	DE

# VS-OE-OE-93J/100,0 - Data cable

1402832

<https://www.phoenixcontact.com/us/products/1402832>

## Technical data

### Product properties

Product type	Data cable by the meter
Number of positions	4
Shielded	yes

### Electrical properties

Transmission medium	Copper
Transmission speed	100 Mbps


### Interfaces

Signal type/category	PROFINET CAT5 (IEC 11801:2002), 100 Mbps
----------------------	--

### Cable/line

Cable length	100 m
--------------	-------

#### PROFINET drag chain CAT5 red [93J]

Dimensional drawing	
Cable weight	61 kg/km
Number of positions	4
Shielded	yes
Cable type	PROFINET drag chain CAT5 red [93J]
Conductor structure	1x4xAWG22/7, SF/TQ
Signal runtime	5.3 ns/m
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Conductor cross-section	4x 0.34 mm <sup>2</sup>
Wire diameter incl. insulation	1.5 mm
External cable diameter	6.50 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	red
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PE
Single wire, color	white, yellow, blue, orange
Thickness, outer sheath	0.90 mm
Overall twist	Star quad

# VS-OE-OE-93J/100,0 - Data cable



1402832

<https://www.phoenixcontact.com/us/products/1402832>

Optical shield covering	85 %
Insulation resistance	≥ 500 MΩ*km
Loop resistance	≤ 120.00 Ω/km
Wave impedance	100 Ω ±15 Ω (at 1 ... 100 MHz)
Nominal voltage, cable	600 V (UL)
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	7.5 x D
Smallest bending radius, fixed installation	33 mm
Smallest bending radius, movable installation	49 mm
Dynamic load capacity (bending)	Max. bending cycles: 3000000, Bending radius: 200 mm, Traversing path: 4 m, Traversing rate: 4 m/s
Tensile strength	≤ 150 N
Flame resistance	according to IEC 60332-1-2
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	UV resistant
Ambient temperature (operation)	-40 °C ... 70 °C (Cable)
Ambient temperature (installation)	-20 °C ... 60 °C

# VS-OE-OE-93J/100,0 - Data cable



1402832

<https://www.phoenixcontact.com/us/products/1402832>

## Classifications

### ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

### ETIM

ETIM 10.0	EC003249
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# VS-OE-OE-93J/100,0 - Data cable



1402832

<https://www.phoenixcontact.com/us/products/1402832>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)